

**NBP1-99123****MMP7 Antibody****Unit Size**

0.1 ml

**Concentration**

1.28 mg/ml

**Storage**

Store at 4C short term. Aliquot and store at -20C long term. Avoid freeze-thaw cycles.

**Applications**

IHC, IHC-P

**Species**

Human, Mouse

**Host**

Rabbit

**Clonality**

Polyclonal

**Purity**

Affinity purified

**Preservative**

0.02% Sodium Azide

**Immunogen**

A synthetic peptide made to an internal portion of the human MMP7 protein (between residues 250-300) [UniProt P09237]

**Recommended Dilutions**

Immunohistochemistry-Paraffin 1:300, Immunohistochemistry

**Buffer**


PBS (pH 7.4)

**Uses**

This MMP7 antibody is useful for Immunohistochemistry-paraffin embedded sections, where staining is seen in the extracellular matrix of human breast cancer. Prior to immunostaining paraffin tissues, antigen retrieval with sodium citrate buffer (pH 6.0) is recommended.

**Images**

Immunohistochemistry: MMP7 Antibody [NBP1-99123] - MMP7 antibody was tested in human breast cancer using DAB with hematoxylin counterstain. The image on the right had the antibody blocked by preincubation with immunizing peptide.



Updated 3/9/2013 2.0

**Limitations:** This product is for research use only and is not approved for use in humans or in clinical diagnosis. Products are guaranteed for six months from the date of receipt except for peptides and proteins which are guaranteed for 3 months. **For more information on our guarantee, please visit [www.novusbio.com/guarantee](http://www.novusbio.com/guarantee).**

**Novus USA**

8100 Southpark Way, A-8  
 Littleton, CO 80120  
 p) 888-506-6887  
 p) 303-730-1950  
 f) 303-730-1966  
[novus@novusbio.com](mailto:novus@novusbio.com)

**Novus Canada**

461 North Service Road West,  
 Unit B37  
 Oakville, ON L6M 2V5  
 p) 855-668-8722  
 f) 905-827-6402  
[canada@novusbio.com](mailto:canada@novusbio.com)

**Novus Europe**

12 Cambridge Science Park  
 Cambridge, UK CB4 0FQ  
 UK: p) +44-1223-426-001, f) +44-871-971-1635  
 DE: p) +49-6922-22340-60, f) +49-0800-58926-79  
 IT: p) +39-02-4032-6786, f) +39-02-4032-6340  
 FR: p) +33-1-76-77-45-30, f) +33-1-76-77-45-31  
[europe@novusbio.com](mailto:europe@novusbio.com)

