

NBP1-99387**GDF3 Protein****Unit Size**

0.02 mg

Concentration

Lyoph

Storage

Store at -20C. Avoid freeze-thaw cycles.

Species

Human

Purity

>95% pure by SDS-PAGE

Specificity/Sensitivity

Unit Definition:N/A

Immunogen

Source: E. coli

Endotoxin Level: <0.1 ng/ug

Activity (Specifications/test method):N/A

Biological activity:Test in process

Results:N/A

Binding Capacity:N/A

Buffer

Sterile filtered and lyophilized with no additive

Reconstitute in H₂O to a concentration of 0.1-1.0 . The solution can then be diluted into other aqueous buffers**Images**

This product does not currently have an image. Earn rewards by submitting your image of this product. Submit a review with your image here: www.novusbio.com/NBP1-99387

Updated 3/9/2013 2.0

Limitations: This product is for research use only and is not approved for use in humans or in clinical diagnosis. Products are guaranteed for six months from the date of receipt except for peptides and proteins which are guaranteed for 3 months. **For more information on our guarantee, please visit www.novusbio.com/guarantee.**

Novus USA

8100 Southpark Way, A-8
 Littleton, CO 80120
 p) 888-506-6887
 p) 303-730-1950
 f) 303-730-1966
novus@novusbio.com

Novus Canada

461 North Service Road West,
 Unit B37
 Oakville, ON L6M 2V5
 p) 855-668-8722
 f) 905-827-6402
canada@novusbio.com

Novus Europe

12 Cambridge Science Park
 Cambridge, UK CB4 0FQ
 UK: p) +44-1223-426-001, f) +44-871-971-1635
 DE: p) +49-6922-22340-60, f) +49-0800-58926-79
 IT: p) +39-02-4032-6786, f) +39-02-4032-6340
 FR: p) +33-1-76-77-45-30, f) +33-1-76-77-45-31
europe@novusbio.com

