

NBP1-77143PEP**TMEM184B Peptide****Unit Size**

0.05 mg

Concentration

0.2 mg/ml

Storage

Store at -20C. Avoid freeze-thaw cycles.

Applications

B/N

Species

Human

Preservative

0.02% Sodium Azide

Immunogen

15 amino acids near the carboxy terminus of human TMEM184B.

Recommended Dilutions

Blocking/Neutralizing

BufferPBS pH 7.2 (10 mM NaH₂PO₄, 10 mM Na₂HPO₄, 130 mM NaCl) containing 0.1% bovine serum albumin.**Uses**

Can be used for blocking the activity of TMEM184B.

ImagesThis product does not currently have an image. Earn rewards by submitting your image of this product. Submit a review with your image here: www.novusbio.com/NBP1-77143PEP

Updated 3/9/2013 2.0

Limitations: This product is for research use only and is not approved for use in humans or in clinical diagnosis. Products are guaranteed for six months from the date of receipt except for peptides and proteins which are guaranteed for 3 months. **For more information on our guarantee, please visit www.novusbio.com/guarantee.**

Novus USA

8100 Southpark Way, A-8
 Littleton, CO 80120
 p) 888-506-6887
 p) 303-730-1950
 f) 303-730-1966
novus@novusbio.com

Novus Canada

461 North Service Road West,
 Unit B37
 Oakville, ON L6M 2V5
 p) 855-668-8722
 f) 905-827-6402
canada@novusbio.com

Novus Europe

12 Cambridge Science Park
 Cambridge, UK CB4 0FQ
 UK: p) +44-1223-426-001, f) +44-871-971-1635
 DE: p) +49-6922-22340-60, f) +49-0800-58926-79
 IT: p) +39-02-4032-6786, f) +39-02-4032-6340
 FR: p) +33-1-76-77-45-30, f) +33-1-76-77-45-31
europe@novusbio.com

