

**NBP1-76476****MAP3K14 Antibody****Unit Size**

0.1 mg

**Concentration**

1 mg/ml

**Storage**

Store at 4C short term. Aliquot and store at -20C long term. Avoid freeze-thaw cycles.

**Applications**

WB, ELISA

**Species**

Human

**Host**

Rabbit

**Clonality**

Polyclonal

**Purity**

Ion exchange chromatography

**Preservative**

0.02% Sodium Azide

**Immunogen**

Antibody was raised against a peptide corresponding to amino acids 931 to 947 of human NIK.

**Recommended Dilutions**

ELISA

Western Blot

**Buffer**

PBS containing 0.02% sodium azide.

**Uses**

NIK antibody can be used for detection of NIK by Western blot.

**Images**This product does not currently have an image. Earn rewards by submitting your image of this product. Submit a review with your image here: [www.novusbio.com/NBP1-76476](http://www.novusbio.com/NBP1-76476)

Updated 3/9/2013 2.0

**Limitations:** This product is for research use only and is not approved for use in humans or in clinical diagnosis. Products are guaranteed for six months from the date of receipt except for peptides and proteins which are guaranteed for 3 months. **For more information on our guarantee, please visit [www.novusbio.com/guarantee](http://www.novusbio.com/guarantee).**

**Novus USA**

8100 Southpark Way, A-8  
 Littleton, CO 80120  
 p) 888-506-6887  
 p) 303-730-1950  
 f) 303-730-1966  
[novus@novusbio.com](mailto:novus@novusbio.com)

**Novus Canada**

461 North Service Road West,  
 Unit B37  
 Oakville, ON L6M 2V5  
 p) 855-668-8722  
 f) 905-827-6402  
[canada@novusbio.com](mailto:canada@novusbio.com)

**Novus Europe**

12 Cambridge Science Park  
 Cambridge, UK CB4 0FQ  
 UK: p) +44-1223-426-001, f) +44-871-971-1635  
 DE: p) +49-6922-22340-60, f) +49-0800-58926-79  
 IT: p) +39-02-4032-6786, f) +39-02-4032-6340  
 FR: p) +33-1-76-77-45-30, f) +33-1-76-77-45-31  
[europe@novusbio.com](mailto:europe@novusbio.com)

