

**NBP1-76618****TSC1 Antibody****Unit Size**

0.1 mg

**Concentration**

1 mg/ml

**Storage**

Store at 4C short term. Aliquot and store at -20C long term. Avoid freeze-thaw cycles.

**Applications**

WB, ELISA, ICC/IF

**Species**

Human, Mouse, Rat

**Host**

Rabbit

**Clonality**

Polyclonal

**Purity**

Affinity purified

**Preservative**

0.02% Sodium Azide

**Immunogen**

Antibody was raised against a 15 amino acid peptide from the middle region of human TSC1. TSC1 antibody will recognize both isoforms of TSC1.

**Recommended Dilutions**

ELISA, Immunocytochemistry/Immunofluorescence, Western Blot

**Buffer**


PBS containing 0.02% sodium azide.

**Uses**

TSC1 antibody can be used for the detection of TSC1 by Western blot at 1 mg/ml.

**Images**

Western Blot: TSC1 Antibody [NBP1-76618] - EL4 cell lysate with TSC1 antibody at 1 ug/ml in the (A) absence and (B) presence of blocking peptide.



Immunocytochemistry/Immunofluorescence: TSC1 Antibody [NBP1-76618] - EL4 cells with TSC1 antibody at 2 ug/ml

Updated 3/9/2013 2.0

**Limitations:** This product is for research use only and is not approved for use in humans or in clinical diagnosis. Products are guaranteed for six months from the date of receipt except for peptides and proteins which are guaranteed for 3 months. **For more information on our guarantee, please visit [www.novusbio.com/guarantee](http://www.novusbio.com/guarantee).**

**Novus USA**
 8100 Southpark Way, A-8  
 Littleton, CO 80120  
 p) 888-506-6887  
 p) 303-730-1950  
 f) 303-730-1966  
[novus@novusbio.com](mailto:novus@novusbio.com)
**Novus Canada**
 461 North Service Road West,  
 Unit B37  
 Oakville, ON L6M 2V5  
 p) 855-668-8722  
 f) 905-827-6402  
[canada@novusbio.com](mailto:canada@novusbio.com)
**Novus Europe**
 12 Cambridge Science Park  
 Cambridge, UK CB4 0FQ  
 UK: p) +44-1223-426-001, f) +44-871-971-1635  
 DE: p) +49-6922-22340-60, f) +49-0800-58926-79  
 IT: p) +39-02-4032-6786, f) +39-02-4032-6340  
 FR: p) +33-1-76-77-45-30, f) +33-1-76-77-45-31  
[europe@novusbio.com](mailto:europe@novusbio.com)
