Orders: orders@novusbio.com
Support: technical@novusbio.com
Web: www.novusbio.com

Protocols, Publications, Related Products, Reviews and more:
www.novusbio.com/NBP1-71814

NBP1-71814

BACH1 Antibody



Unit Size
0.1 mg

Concentration
1 mg/ml

Storage
Store at 4C. Do not freeze.

Applications
WB, IP

Species
Human

Molecular Weight
82kDa

Host
Rabbit

Clonality
Polyclonal

Purity
Immunogen affinity purified

Preservative
0.09% Sodium Azide

Updated 3/9/2013 2.0

Immunogen
The immunogen for this product maps to a region between residue 350 and 400 of human BTB and CNC Homology 1, Basic Leucine Zipper Transcription Factor 1 using the numbering given in entry NP_001177.1 (GeneID 571).

Recommended Dilutions
Immunoprecipitation 2-5 ug/mg lysate, Western Blot 1:2000 - 1:10000

Buffer
Tris-citrate/phosphate buffer, pH 7 to 8

Uses
This antibody works in Western Blot, Immunoprecipitation.

Images
Western Blot: BACH1 Antibody [NBP1-71814] - Whole cell lysate from HeLa (5, 15 and 50 mcg for WB; 1 mg for IP, 20% of IP loaded) and 293T (T; 50 mcg) cells. Affinity purified rabbit anti-BACH1 antibody used for WB at 0.1 mcg/ml (A) and 1 mcg... See more at www.novusbio.com/NBP1-71814



Limitations: This product is for research use only and is not approved for use in humans or in clinical diagnosis. Products are guaranteed for six months from the date of receipt except for peptides and proteins which are guaranteed for 3 months. ***For more information on our guarantee, please visit www.novusbio.com/guarantee.***

Novus USA
8100 Southpark Way, A-8
Littleton, CO 80120
p) 888-506-6887
p) 303-730-1950
f) 303-730-1966
novus@novusbio.com

Novus Canada
461 North Service Road West,
Unit B37
Oakville, ON L6M 2V5
p) 855-668-8722
f) 905-827-6402
canada@novusbio.com

Novus Europe
12 Cambridge Science Park
Cambridge, UK CB4 0FQ
UK: p) +44-1223-426-001, f) +44-871-971-1635
DE: p) +49-6922-22340-60, f) +49-0800-58926-79
IT: p) +39-02-4032-6786, f) +39-02-4032-6340
FR: p) +33-1-76-77-45-30, f) +33-1-76-77-45-31
europe@novusbio.com