

**NBP1-69421****UGT3A2 Antibody****Unit Size**

0.1 mg

**Concentration**

lyoph

**Storage**

Store at -20C. Avoid freeze-thaw cycles.

**Applications**

WB

**Species**

Human

**Host**

Rabbit

**Clonality**

Polyclonal

**Purity**

IgG purified

**Preservative**

No Preservative

**Immunogen**

Synthetic peptides corresponding to UGT3A2(UDP glycosyltransferase 3 family, polypeptide A2) The peptide sequence was selected from the N terminal of UGT3A2. Peptide sequence HNVTMLNHKRGPFMPDFKKEEKSYQVISWLAPEDHQREFKKSFDFFLEET.

**Recommended Dilutions**

Western Blot

**Buffer**

PBS & 2% Sucrose lyophilized with the antibody. Centrifuge the vial of lyoph antibody at 12,000 x g for 20 seconds. Add 100ul of distilled water. Vortex followed by centrifuge again to pellet the solution. Final concentration is 1 mg/ml in PBS buffer

**Uses**

This is a rabbit polyclonal antibody against UGT3A2 and was validated on Western blot.

**Images**

Western Blot: UGT3A2 Antibody [NBP1-69421] - This Anti-UGT3A2 antibody was used in Western Blot of HepG2 tissue lysate at a concentration of 2.5ug/ml.



Updated 3/9/2013 2.0

**Limitations:** This product is for research use only and is not approved for use in humans or in clinical diagnosis. Products are guaranteed for six months from the date of receipt except for peptides and proteins which are guaranteed for 3 months. **For more information on our guarantee, please visit [www.novusbio.com/guarantee](http://www.novusbio.com/guarantee).**

**Novus USA**

8100 Southpark Way, A-8  
 Littleton, CO 80120  
 p) 888-506-6887  
 p) 303-730-1950  
 f) 303-730-1966  
[novus@novusbio.com](mailto:novus@novusbio.com)

**Novus Canada**

461 North Service Road West,  
 Unit B37  
 Oakville, ON L6M 2V5  
 p) 855-668-8722  
 f) 905-827-6402  
[canada@novusbio.com](mailto:canada@novusbio.com)

**Novus Europe**

12 Cambridge Science Park  
 Cambridge, UK CB4 0FQ  
 UK: p) +44-1223-426-001, f) +44-871-971-1635  
 DE: p) +49-6922-22340-60, f) +49-0800-58926-79  
 IT: p) +39-02-4032-6786, f) +39-02-4032-6340  
 FR: p) +33-1-76-77-45-30, f) +33-1-76-77-45-31  
[europe@novusbio.com](mailto:europe@novusbio.com)

