

**NBP1-60082****SLC6A8 Antibody****Unit Size**

0.1 mg

**Concentration**

Lyoph

**Storage**

Store at -20C. Avoid freeze-thaw cycles.

**Applications**

WB, IHC, IHC-P

**Species**

Human, Mouse, Rat, Canine

**Host**

Rabbit

**Clonality**

Polyclonal

**Purity**

IgG purified

**Preservative**

No Preservative

**Immunogen**

Synthetic peptides corresponding to SLC6A8(solute carrier family 6 (neurotransmitter transporter, creatine), member 8) The peptide sequence was selected from the N terminal of SLC6A8. Peptide sequence CDQLADRRSPVIEFWENKVLRLSGGLEVP GALNWEVTL

**Recommended Dilutions**

Immunohistochemistry, Immunohistochemistry-Paraffin, Western Blot

**Buffer**

PBS & 2% Sucrose lyophilized with the antibody. Centrifuge the vial of lyoph antibody at 12,000 x g for 20 seconds. Add 100ul of distilled water. Vortex followed by centrifuge again to pellet the solution. Final concentration is 1 mg/ml in PBS buffer

**Uses**

This is a rabbit polyclonal antibody against SLC6A8 and was validated on Western Blot and immunohistochemistry-paraffin

**Images**

Western Blot: SLC6A8 Antibody [NBP1-60082] - MDA-MB-435S cell lysate, Antibody Titration: 2.5ug/ml



Immunohistochemistry-Paraffin: SLC6A8 Antibody [NBP1-60082] - Human Muscle Tissue, Skeletal muscle cells (Indicated with Arrows) 4-8ug/ml.



Updated 3/9/2013 2.0

**Limitations:** This product is for research use only and is not approved for use in humans or in clinical diagnosis. Products are guaranteed for six months from the date of receipt except for peptides and proteins which are guaranteed for 3 months. **For more information on our guarantee, please visit [www.novusbio.com/guarantee](http://www.novusbio.com/guarantee).**

**Novus USA**

8100 Southpark Way, A-8  
 Littleton, CO 80120  
 p) 888-506-6887  
 p) 303-730-1950  
 f) 303-730-1966  
[novus@novusbio.com](mailto:novus@novusbio.com)

**Novus Canada**

461 North Service Road West,  
 Unit B37  
 Oakville, ON L6M 2V5  
 p) 855-668-8722  
 f) 905-827-6402  
[canada@novusbio.com](mailto:canada@novusbio.com)

**Novus Europe**

12 Cambridge Science Park  
 Cambridge, UK CB4 0FQ  
 UK: p) +44-1223-426-001, f) +44-871-971-1635  
 DE: p) +49-6922-22340-60, f) +49-0800-58926-79  
 IT: p) +39-02-4032-6786, f) +39-02-4032-6340  
 FR: p) +33-1-76-77-45-30, f) +33-1-76-77-45-31  
[europe@novusbio.com](mailto:europe@novusbio.com)

