

NBP1-57092**MMP19 Antibody****Unit Size**

0.05 mg

Concentration

Lyoph

Storage

Store at -20C. Avoid freeze-thaw cycles.

Applications

WB, IHC, IHC-P

Species

Human, Canine

Host

Rabbit

Clonality

Polyclonal

Purity

Peptide affinity purified

Preservative

No Preservative

Immunogen

Synthetic peptides corresponding to MMP19 (matrix metalloproteinase 19) The peptide sequence was selected from the N terminal of MMP19 . Peptide sequence ALRAFQEASELPVSGQLDDATRRMRQPRCGLEDPFNQKTLKYLGRWR.

Recommended Dilutions

Immunohistochemistry, Immunohistochemistry-Paraffin, Western Blot

Buffer

PBS & 2% Sucrose lyophilized with the antibody. Centrifuge the vial of lyoph antibody at 12,000 x g for 20 seconds. Add 50ul of distilled water. Vortex followed by centrifuge again to pellet the solution. Final concentration is 1 mg/ml in PBS buffer

Uses

This is a rabbit polyclonal antibody against MMP19 and was validated on Western Blot and immunohistochemistry-p

Images (more available at www.novusbio.com/NBP1-57092)

Western Blot: MMP19 Antibody [NBP1-57092] -
 HepG2 cell lysate, Antibody Titration: 0.2-1 ug/ml



Immunohistochemistry-Paraffin: MMP19 Antibody
 [NBP1-57092] - Human urinary bladder tissue,
 Ganglionic cells (Indicated with Arrows) 4-8ug/ml.



Updated 3/9/2013 2.0

Limitations: This product is for research use only and is not approved for use in humans or in clinical diagnosis. Products are guaranteed for six months from the date of receipt except for peptides and proteins which are guaranteed for 3 months. **For more information on our guarantee, please visit www.novusbio.com/guarantee.**

Novus USA

8100 Southpark Way, A-8
 Littleton, CO 80120
 p) 888-506-6887
 p) 303-730-1950
 f) 303-730-1966
novus@novusbio.com

Novus Canada

461 North Service Road West,
 Unit B37
 Oakville, ON L6M 2V5
 p) 855-668-8722
 f) 905-827-6402
canada@novusbio.com

Novus Europe

12 Cambridge Science Park
 Cambridge, UK CB4 0FQ
 UK: p) +44-1223-426-001, f) +44-871-971-1635
 DE: p) +49-6922-22340-60, f) +49-0800-58926-79
 IT: p) +39-02-4032-6786, f) +39-02-4032-6340
 FR: p) +33-1-76-77-45-30, f) +33-1-76-77-45-31
europe@novusbio.com

