

NBP1-50321**Uromodulin Antibody (10.32)****Unit Size**

0.05 mg

Concentration

Concentrations vary lot to lot. See vial label for concentration.

Storage

Store at 4C short term. Aliquot and store at -20C long term. Avoid freeze-thaw cycles.

Applications

ICC/IF, IHC, IHC-Fr, IHC-P

Species

Human

Host

Mouse

Clonality

Monoclonal

Isotype

IgG2b

Purity

Protein G purified

Preservative

0.02% Sodium Azide

Specificity/Sensitivity

Anti-human Tamm-Horsfall protein (THP) is a monoclonal antibody which reacts with an epitope of the urinary mucoprotein. Tamm-Horsfall protein is a glycoprotein of approximately 80 kD containing up to 25% carbohydrate by weight.

Immunogen

Human Tamm-Horsfall protein

Recommended Dilutions

Immunocytochemistry/Immunofluorescence, Immunohistochemistry, Immunohistochemistry-Frozen, Immunohistochemistry-Paraffin 20 ug/ml

Buffer

PBS

Uses

For IHC-Paraffin, use heat induced antigen retrieval in pH 6.0 citrate buffer.

Images

Immunohistochemistry-Paraffin: Uromodulin Antibody (10.32) [NBP1-50321] - Staining of human kidney. Immunohistochemistry of formalin-fixed, paraffin-embedded tissue after heat-induced antigen retrieval. Antibody concentration 20 ug/ml.



Updated 3/9/2013 2.0

Limitations: This product is for research use only and is not approved for use in humans or in clinical diagnosis. Products are guaranteed for six months from the date of receipt except for peptides and proteins which are guaranteed for 3 months. **For more information on our guarantee, please visit www.novusbio.com/guarantee.**

Novus USA

8100 Southpark Way, A-8
 Littleton, CO 80120
 p) 888-506-6887
 p) 303-730-1950
 f) 303-730-1966
novus@novusbio.com

Novus Canada

461 North Service Road West,
 Unit B37
 Oakville, ON L6M 2V5
 p) 855-668-8722
 f) 905-827-6402
canada@novusbio.com

Novus Europe

12 Cambridge Science Park
 Cambridge, UK CB4 0FQ
 UK: p) +44-1223-426-001, f) +44-871-971-1635
 DE: p) +49-6922-22340-60, f) +49-0800-58926-79
 IT: p) +39-02-4032-6786, f) +39-02-4032-6340
 FR: p) +33-1-76-77-45-30, f) +33-1-76-77-45-31
europe@novusbio.com

