

NBP1-47520**Yes1 Antibody (2F3E6)****Unit Size**

0.1 ml

Concentration

This product is unpurified. The exact concentration of antibody is not quantifiable.

Storage

Store at 4C short term. Aliquot and store at -20C long term. Avoid freeze-thaw cycles.

Applications

WB, ELISA

Species

Human

Host

Mouse

Clonality

Monoclonal

Isotype

IgG1

Purity

Ascites

Preservative

0.03% Sodium Azide

Immunogen

Purified recombinant fragment of YES(aa10-193) expressed in E. Coli.

Recommended Dilutions

Western Blot 1: 500 - 1:2000

ELISA 1:10000

Buffer

Ascites

Uses

This antibody is useful in Western Blot, ELISA.

Images

Western Blot: YES1 Antibody (2F3E6) [NBP1-47520] - Western blot analysis using anti-YES1 monoclonal antibody against truncated YES1-His recombinant protein(1) and full-length GFP-YES1 (aa1-543) transfected COS7 cell lysate(2).



Updated 3/9/2013 2.0

Limitations: This product is for research use only and is not approved for use in humans or in clinical diagnosis. Products are guaranteed for six months from the date of receipt except for peptides and proteins which are guaranteed for 3 months. **For more information on our guarantee, please visit www.novusbio.com/guarantee.**

Novus USA

8100 Southpark Way, A-8
 Littleton, CO 80120
 p) 888-506-6887
 p) 303-730-1950
 f) 303-730-1966
novus@novusbio.com

Novus Canada

461 North Service Road West,
 Unit B37
 Oakville, ON L6M 2V5
 p) 855-668-8722
 f) 905-827-6402
canada@novusbio.com

Novus Europe

12 Cambridge Science Park
 Cambridge, UK CB4 0FQ
 UK: p) +44-1223-426-001, f) +44-871-971-1635
 DE: p) +49-6922-22340-60, f) +49-0800-58926-79
 IT: p) +39-02-4032-6786, f) +39-02-4032-6340
 FR: p) +33-1-76-77-45-30, f) +33-1-76-77-45-31
europe@novusbio.com

