

NBP1-49463**THAP11 Antibody****Unit Size**

0.1 ml

Concentration

This product is unpurified. The exact concentration of antibody is not quantifiable.

Storage

Store at -20C. Avoid freeze-thaw cycles.

Applications

WB, ICC/IF, IHC, IHC-P

Species

Human, Mouse, Rat, Bovine

Molecular Weight

26kDa

Host

Rabbit

Clonality

Polyclonal

Purity

Whole antisera

Preservative

0.1% Sodium Azide

Immunogen

Partial recombinant human THAP11 protein expressed in E. coli [Swiss-Prot# Q96EK4]

Recommended Dilutions


Immunocytochemistry/Immunofluorescence 1:1000, Immunohistochemistry, Immunohistochemistry-Paraffin 1:300, Western Blot 1:10000

Uses

This THAP11 antibody is useful for Immunocytochemistry/Immunofluorescence, Immunohistochemistry on paraffin-embedded sections and Western blot, where a band is seen at ~26 kDa.

Images (more available at www.novusbio.com/NBP1-49463)

Western Blot: THAP11 Antibody [NBP1-49463] - Analysis of THAP11 in HeLa whole cell extracts.



Immunocytochemistry/Immunofluorescence:
 THAP11 Antibody [NBP1-49463] -
 Immunocytochemical analysis of THAP11 in HeLa cells.



Updated 3/9/2013 2.0

Limitations: This product is for research use only and is not approved for use in humans or in clinical diagnosis. Products are guaranteed for six months from the date of receipt except for peptides and proteins which are guaranteed for 3 months. **For more information on our guarantee, please visit www.novusbio.com/guarantee.**

Novus USA

8100 Southpark Way, A-8
 Littleton, CO 80120
 p) 888-506-6887
 p) 303-730-1950
 f) 303-730-1966
novus@novusbio.com

Novus Canada

461 North Service Road West,
 Unit B37
 Oakville, ON L6M 2V5
 p) 855-668-8722
 f) 905-827-6402
canada@novusbio.com

Novus Europe

12 Cambridge Science Park
 Cambridge, UK CB4 0FQ
 UK: p) +44-1223-426-001, f) +44-871-971-1635
 DE: p) +49-6922-22340-60, f) +49-0800-58926-79
 IT: p) +39-02-4032-6786, f) +39-02-4032-6340
 FR: p) +33-1-76-77-45-30, f) +33-1-76-77-45-31
europe@novusbio.com

