

NBP1-49534C**TIGAR Antibody [DyLight 650]****Unit Size**

0.1 ml

Concentration

0.5 mg/ml

Storage

Store at 4C in the dark.

Applications

WB, IHC

Species

Human, Mouse

Host

Rabbit

Clonality

Polyclonal

Conjugate

DyLight 650

Purity

Affinity purified

Preservative

No Preservative

Immunogen

A genomic peptide made to an internal region of the human TIGAR protein (within residues 50-200). [Swiss-Prot Q9NQ88]

Recommended Dilutions

Immunohistochemistry 1:150

Western Blot 1:5000

Buffer

50mM sodium borate

Uses

This TIGAR antibody is useful for Immunohistochemistry and Western blot. In Western blot bands are seen ~30 kDa, representing TIGAR, and ~47 kDa. At this time we cannot explain the band at 47 kDa. This antibody does not appear to work in ICC.

Images

This product does not currently have an image. Earn rewards by submitting your image of this product. Submit a review with your image here: www.novusbio.com/NBP1-49534C

Updated 3/9/2013 2.0

Limitations: This product is for research use only and is not approved for use in humans or in clinical diagnosis. Products are guaranteed for six months from the date of receipt except for peptides and proteins which are guaranteed for 3 months. **For more information on our guarantee, please visit www.novusbio.com/guarantee.**

Novus USA

8100 Southpark Way, A-8
 Littleton, CO 80120
 p) 888-506-6887
 p) 303-730-1950
 f) 303-730-1966
novus@novusbio.com

Novus Canada

461 North Service Road West,
 Unit B37
 Oakville, ON L6M 2V5
 p) 855-668-8722
 f) 905-827-6402
canada@novusbio.com

Novus Europe

12 Cambridge Science Park
 Cambridge, UK CB4 0FQ
 UK: p) +44-1223-426-001, f) +44-871-971-1635
 DE: p) +49-6922-22340-60, f) +49-0800-58926-79
 IT: p) +39-02-4032-6786, f) +39-02-4032-6340
 FR: p) +33-1-76-77-45-30, f) +33-1-76-77-45-31
europe@novusbio.com

