

NBP1-46768**SHANK3 Antibody****Unit Size**

0.5 mg

Concentration

Lyoph

Storage

Store at 4C short term. Aliquot and store at -20C long term. Avoid freeze-thaw cycles.

Applications

WB, IHC, IHC-Fr, IHC-P

Species

Human, Mouse, Rat

Molecular Weight

186kDa

Host

Rabbit

Clonality

Polyclonal

Purity

IgG purified

Preservative

No Preservative

Immunogen

A synthetic peptide from the internal part of human SHANK3 (SH3 and multiple ankyrin repeat domains protein 3, ProSAP2) conjugated to an immunogenic carrier protein was used as the antigen.

Recommended Dilutions

Immunohistochemistry-Frozen 10-50 ug/ml, Immunohistochemistry-Paraffin 10-50 ug/ml, Western Blot 10-50 ug/ml, Immunohistochemistry

Buffer

Lyophilized. Reconstitute in 500 ul of sterile water. Centrifuge to remove any insoluble material.

Uses

Immunohistochemistry-Paraffin/Frozen, Western Blot. A concentration of 10-50 µg/ml is recommended. The optimal concentration should be determined by the end user. Not yet tested in other applications.

ImagesThis product does not currently have an image. Earn rewards by submitting your image of this product. Submit a review with your image here: www.novusbio.com/NBP1-46768

Updated 3/9/2013 2.0

Limitations: This product is for research use only and is not approved for use in humans or in clinical diagnosis. Products are guaranteed for six months from the date of receipt except for peptides and proteins which are guaranteed for 3 months. **For more information on our guarantee, please visit www.novusbio.com/guarantee.**

Novus USA

8100 Southpark Way, A-8
 Littleton, CO 80120
 p) 888-506-6887
 p) 303-730-1950
 f) 303-730-1966
novus@novusbio.com

Novus Canada

461 North Service Road West,
 Unit B37
 Oakville, ON L6M 2V5
 p) 855-668-8722
 f) 905-827-6402
canada@novusbio.com

Novus Europe

12 Cambridge Science Park
 Cambridge, UK CB4 0FQ
 UK: p) +44-1223-426-001, f) +44-871-971-1635
 DE: p) +49-6922-22340-60, f) +49-0800-58926-79
 IT: p) +39-02-4032-6786, f) +39-02-4032-6340
 FR: p) +33-1-76-77-45-30, f) +33-1-76-77-45-31
europe@novusbio.com

