

NBP1-33531**Merlin Antibody****Unit Size**

0.1 mg

Concentration

Concentrations vary lot to lot. See vial label for concentration.

Storage

Store at -20C. Avoid freeze-thaw cycles.

Applications

WB, IHC, IHC-P

Species

Human, Mouse, Rat

Molecular Weight

70kDa

Host

Rabbit

Clonality

Polyclonal

Purity

Immunogen affinity purified

Preservative

0.01% Thimerosal

Marker

Plasma Membrane Marker

Immunogen

Recombinant protein fragment contain a sequence corresponding to a region within amino acids 1 and 172 of Neurofibromin 2

Recommended Dilutions


Immunohistochemistry 1:100-1:1000, Immunohistochemistry-Paraffin 1:100-1:1000, Western Blot 1:1000-1:10000

Buffer

0.1M Tris, 0.1M Glycine, 20% Glycerol (pH7).

Images (more available at www.novusbio.com/NBP1-33531)

Western Blot: Merlin Antibody [NBP1-33531] - Sample (30 ug of whole cell lysate) A: A431 B: H1299 C: Hela 7. 5% SDS PAGE; antibody diluted at 1:1000.



Immunohistochemistry-Paraffin: Merlin Antibody [NBP1-33531] - Paraffin-embedded RT2 xenograft, using Neurofibromin 2 antibody at 1:500 dilution.



Updated 3/9/2013 2.0

Limitations: This product is for research use only and is not approved for use in humans or in clinical diagnosis. Products are guaranteed for six months from the date of receipt except for peptides and proteins which are guaranteed for 3 months. **For more information on our guarantee, please visit www.novusbio.com/guarantee.**

Novus USA

8100 Southpark Way, A-8
 Littleton, CO 80120
 p) 888-506-6887
 p) 303-730-1950
 f) 303-730-1966
novus@novusbio.com

Novus Canada

461 North Service Road West,
 Unit B37
 Oakville, ON L6M 2V5
 p) 855-668-8722
 f) 905-827-6402
canada@novusbio.com

Novus Europe

12 Cambridge Science Park
 Cambridge, UK CB4 0FQ
 UK: p) +44-1223-426-001, f) +44-871-971-1635
 DE: p) +49-6922-22340-60, f) +49-0800-58926-79
 IT: p) +39-02-4032-6786, f) +39-02-4032-6340
 FR: p) +33-1-76-77-45-30, f) +33-1-76-77-45-31
europe@novusbio.com

