

NBP1-40254**Prothrombin Antibody (8.H.11)****Unit Size**

0.05 mg

Concentration

Concentrations vary lot to lot. See vial label for concentration.

Storage

Store at 4C short term. Aliquot and store at -20C long term. Avoid freeze-thaw cycles.

Applications

WB, ELISA, IHC, IHC-P

Species

Human

Host

Mouse

Clonality

Monoclonal

Isotype

IgG2a

Purity

Ion exchange chromatography

Preservative

No Preservative

Immunogen

Recognizes human Prothrombin, prethrombin-1, fragment 2, meizothrombin. Inhibits clotting and prothrombin activation.

Recommended Dilutions

ELISA 5-10

Immunohistochemistry

Immunohistochemistry-Paraffin 5 ug/ml

Western Blot 10 ug/ml

Buffer50% glycerol, dH₂O.**Uses**

Recommended dilutions for ELISA: Coating 5-10 ug/ml. Detection: 100-1000 ug/ml.

Images

Immunohistochemistry-Paraffin: Prothrombin Antibody (8.H.11) [NBP1-40254] - Staining of human liver. Immunohistochemistry of formalin-fixed, paraffin-embedded tissue after heat-induced antigen retrieval. Antibody concentration 5 ug/ml.



Updated 3/9/2013 2.0

Limitations: This product is for research use only and is not approved for use in humans or in clinical diagnosis. Products are guaranteed for six months from the date of receipt except for peptides and proteins which are guaranteed for 3 months. For more information on our guarantee, please visit www.novusbio.com/guarantee.

Novus USA

8100 Southpark Way, A-8
 Littleton, CO 80120
 p) 888-506-6887
 p) 303-730-1950
 f) 303-730-1966
novus@novusbio.com

Novus Canada

461 North Service Road West,
 Unit B37
 Oakville, ON L6M 2V5
 p) 855-668-8722
 f) 905-827-6402
canada@novusbio.com

Novus Europe

12 Cambridge Science Park
 Cambridge, UK CB4 0FQ
 UK: p) +44-1223-426-001, f) +44-871-971-1635
 DE: p) +49-6922-22340-60, f) +49-0800-58926-79
 IT: p) +39-02-4032-6786, f) +39-02-4032-6340
 FR: p) +33-1-76-77-45-30, f) +33-1-76-77-45-31
europe@novusbio.com

