

NBP1-40993**TECK Antibody****Unit Size**

0.05 mg

Concentration

Lyoph

Storage

Store at 4C short term. Aliquot and store at -20C long term. Avoid freeze-thaw cycles.

Applications

WB, ELISA, Func, IHC, IHC-P

Species

Human

Host

Rabbit

Clonality

Polyclonal

Purity

IgG purified

Preservative

0.09% Sodium Azide

Immunogen

Recombinant human CCL25 (TECK)

Recommended Dilutions

ELISA 0.5-2.0 ug/ml, Western Blot 0.1-0.2 ug/ml, Functional 10.0-15.0 ug/ml, Immunohistochemistry-Paraffin 0.5-1.0 ug/ml, Immunohistochemistry

Buffer

Lyophilized from PBS, pH7.2

Uses

For IHC-P: This product requires protein digestion pre-treatment of paraffin sections e.g. trypsin or pronase.

Images

Immunohistochemistry-Paraffin: TECK Antibody [NBP1-40993] Formalin fixed, paraffin embedded normal human small bowel stained with Rabbit anti Human TECK following antigen retrieval with proteinase k

Immunohistochemistry-Paraffin: TECK Antibody [NBP1-40993] - Immunohistochemistry-Paraffin: TECK Antibody [NBP1-40993] Normal human small bowel stained with Rabbit anti Human CCL25 following antigen retrieval with proteinase k.



Updated 3/9/2013 2.0

Limitations: This product is for research use only and is not approved for use in humans or in clinical diagnosis. Products are guaranteed for six months from the date of receipt except for peptides and proteins which are guaranteed for 3 months. **For more information on our guarantee, please visit www.novusbio.com/guarantee.**

Novus USA

8100 Southpark Way, A-8
 Littleton, CO 80120
 p) 888-506-6887
 p) 303-730-1950
 f) 303-730-1966
novus@novusbio.com

Novus Canada

461 North Service Road West,
 Unit B37
 Oakville, ON L6M 2V5
 p) 855-668-8722
 f) 905-827-6402
canada@novusbio.com

Novus Europe

12 Cambridge Science Park
 Cambridge, UK CB4 0FQ
 UK: p) +44-1223-426-001, f) +44-871-971-1635
 DE: p) +49-6922-22340-60, f) +49-0800-58926-79
 IT: p) +39-02-4032-6786, f) +39-02-4032-6340
 FR: p) +33-1-76-77-45-30, f) +33-1-76-77-45-31
europe@novusbio.com

