

NBP1-32521**SUCLG2 Antibody****Unit Size**

0.1 ml

Concentration

Concentrations vary lot to lot. See vial label for concentration.

Storage

Aliquot and store at -20C or -80C. Avoid freeze-thaw cycles.

Applications

WB, ICC/IF

Species

Human, Mouse

Host

Rabbit

Clonality

Polyclonal

Purity

Immunogen affinity purified

Preservative

0.01% Thimerosal

Immunogen

Recombinant fragment corresponding to a region within amino acids 1 and 234 of SUCLG2.

Recommended Dilutions


Immunocytochemistry/Immunofluorescence 1:100-1:1000, Western Blot 1:500-1:3000

Buffer

0.1M Tris, 0.1M Glycine, 10% Glycerol (pH7.0).

Images (more available at www.novusbio.com/NBP1-32521)

Western Blot: SUCLG2 Antibody [NBP1-32521] -
 Sample(30ug whole cell lysate)A: 293TB: A431 C:
 H1299D: HeLa S3 E: Hep G2 F: MOLT4 G: Raji
 10% SDS PAGE, antibody diluted at 1:1000.



Immunocytochemistry/Immunofluorescence:
 SUCLG2 Antibody [NBP1-32521] - Methanol-fixed
 HeLa, using SUCLG2 antibody at 1:200 dilution.



Updated 3/9/2013 2.0

Limitations: This product is for research use only and is not approved for use in humans or in clinical diagnosis. Products are guaranteed for six months from the date of receipt except for peptides and proteins which are guaranteed for 3 months. **For more information on our guarantee, please visit www.novusbio.com/guarantee.**

Novus USA

8100 Southpark Way, A-8
 Littleton, CO 80120
 p) 888-506-6887
 p) 303-730-1950
 f) 303-730-1966
novus@novusbio.com

Novus Canada

461 North Service Road West,
 Unit B37
 Oakville, ON L6M 2V5
 p) 855-668-8722
 f) 905-827-6402
canada@novusbio.com

Novus Europe

12 Cambridge Science Park
 Cambridge, UK CB4 0FQ
 UK: p) +44-1223-426-001, f) +44-871-971-1635
 DE: p) +49-6922-22340-60, f) +49-0800-58926-79
 IT: p) +39-02-4032-6786, f) +39-02-4032-6340
 FR: p) +33-1-76-77-45-30, f) +33-1-76-77-45-31
europe@novusbio.com

