

NBP1-33021**ATP6V1A Antibody****Unit Size**

0.1 ml

Concentration

Concentrations vary lot to lot. See vial label for concentration.

Storage

Store at -20C. Avoid freeze-thaw cycles.

Applications

WB, ICC/IF

Species

Human

Host

Rabbit

Clonality

Polyclonal

Purity

Affinity purified

Preservative

0.01% Thimerosal

Immunogen

Recombinant fragment corresponding to a region within amino acids 60 and 344 of ATP6V1A (Uniprot ID#P38606)

Recommended Dilutions

Immunocytochemistry/Immunofluorescence, Western Blot 1:500-1:3000

Buffer

0.1M Tris, 0.1M Glycine, 10% Glycerol (pH7.0).

Uses


Western blot. The usefulness of this product in other applications has not been determined.

References


Bacac M, Fusco C, Planche A et al Securin and separase modulate membrane traffic by affecting endosomal acidification Traffic 2011 May [PMID: 21272169] (ICC/IF, Human)

Images (more available at www.novusbio.com/NBP1-33021)

Western Blot: ATP6V1A Antibody [NBP1-33021] - Sample (30 ug of whole cell lysate) A: HeLa B: Hep G2 7. 5% SDS PAGE; antibody diluted at 1:10000.



Immunocytochemistry/Immunofluorescence: ATP6V1A Antibody [NBP1-33021] - Analysis of methanol-fixed A431, using antibody at 1:500 dilution.



Updated 3/9/2013 2.0

Limitations: This product is for research use only and is not approved for use in humans or in clinical diagnosis. Products are guaranteed for six months from the date of receipt except for peptides and proteins which are guaranteed for 3 months. **For more information on our guarantee, please visit www.novusbio.com/guarantee.**

Novus USA
 8100 Southpark Way, A-8
 Littleton, CO 80120
 p) 888-506-6887
 p) 303-730-1950
 f) 303-730-1966
novus@novusbio.com
Novus Canada
 461 North Service Road West,
 Unit B37
 Oakville, ON L6M 2V5
 p) 855-668-8722
 f) 905-827-6402
canada@novusbio.com
Novus Europe
 12 Cambridge Science Park
 Cambridge, UK CB4 0FQ
 UK: p) +44-1223-426-001, f) +44-871-971-1635
 DE: p) +49-6922-22340-60, f) +49-0800-58926-79
 IT: p) +39-02-4032-6786, f) +39-02-4032-6340
 FR: p) +33-1-76-77-45-30, f) +33-1-76-77-45-31
europe@novusbio.com
