

NBP1-28407**VCAM1 Antibody (1.G11B1) [R-Phycoerythrin]****Unit Size**

1.0 ml

Concentration

Please see the vial label for concentration.

Storage

Store at 4C. Do not freeze.

Applications

WB, ELISA, FLOW, IHC, IHC-Fr

Species

Human

Host

Mouse

Clonality

Monoclonal

Isotype

IgG1

Conjugate

R-Phycoerythrin

Purity

IgG purified

Preservative

Sodium Azide

Specificity/Sensitivity

Human CD106/VCAM-1

Immunogen

The immunogen is a peptide made to the amino acid region VCAM1

Recommended DilutionsFlow Cytometry 10 μ L/10⁶ cells, ELISA, Western Blot, Immunohistochemistry-Frozen, Immunohistochemistry**Buffer**1.0 mL of PBS/NaN₃ and a stabilizing agent**Uses**

Flow Cytometry, ELISA, Western Blot and Immunohistochemistry-Frozen

ImagesThis product does not currently have an image. Earn rewards by submitting your image of this product. Submit a review with your image here: www.novusbio.com/NBP1-28407**Notes**

Protect conjugated forms from light.

Updated 3/9/2013 2.0

Limitations: This product is for research use only and is not approved for use in humans or in clinical diagnosis. Products are guaranteed for six months from the date of receipt except for peptides and proteins which are guaranteed for 3 months. For more information on our guarantee, please visit www.novusbio.com/guarantee.

Novus USA

8100 Southpark Way, A-8
 Littleton, CO 80120
 p) 888-506-6887
 p) 303-730-1950
 f) 303-730-1966
novus@novusbio.com

Novus Canada

461 North Service Road West,
 Unit B37
 Oakville, ON L6M 2V5
 p) 855-668-8722
 f) 905-827-6402
canada@novusbio.com

Novus Europe

12 Cambridge Science Park
 Cambridge, UK CB4 0FQ
 UK: p) +44-1223-426-001, f) +44-871-971-1635
 DE: p) +49-6922-22340-60, f) +49-0800-58926-79
 IT: p) +39-02-4032-6786, f) +39-02-4032-6340
 FR: p) +33-1-76-77-45-30, f) +33-1-76-77-45-31
europe@novusbio.com

