

NBP1-28559**BCL2L1 Antibody (7B2.5)****Unit Size**

0.05 mg

Concentration

0.1 mg/ml

Storage

Store at 4C. Do not freeze.

Applications

WB, FLOW, IHC, IHC-Fr, IP

Species

Human

Host

Mouse

Clonality

Monoclonal

Isotype

IgG3

Purity

IgG purified

Preservative

No Preservative

Specificity/Sensitivity

Human Bcl-xL (Mr 29 kDa)

Immunogen

Recombinant Bcl-xS

Recommended DilutionsImmunoprecipitation, Western Blot, Immunohistochemistry-Frozen, Immunohistochemistry, Flow Cytometry < = 3 ug/10⁶ cells**Buffer**

1.0 mL of 100 mM borate buffered saline, pH 8.0.

Uses

Flow Cytometry, Immunoprecipitation, Western Blot and Immunohistochemistry-Frozen

Images

Flow cytometry: Bcl-xL Antibody (7B2.5) [NBP1-28559] - 2 ug/10⁶ Murine FL5 cells (FL5-NEO) and FL5 cells transfected with Bcl-xL expression plasmid (FL5-BCL-XL) were fixed with buffered paraformaldehyde and then permeabilized with saponin. ... See more at www.novusbio.com/NBP1-28559



Updated 3/9/2013 2.0

Limitations: This product is for research use only and is not approved for use in humans or in clinical diagnosis. Products are guaranteed for six months from the date of receipt except for peptides and proteins which are guaranteed for 3 months. **For more information on our guarantee, please visit www.novusbio.com/guarantee.**

Novus USA

8100 Southpark Way, A-8
 Littleton, CO 80120
 p) 888-506-6887
 p) 303-730-1950
 f) 303-730-1966
novus@novusbio.com

Novus Canada

461 North Service Road West,
 Unit B37
 Oakville, ON L6M 2V5
 p) 855-668-8722
 f) 905-827-6402
canada@novusbio.com

Novus Europe

12 Cambridge Science Park
 Cambridge, UK CB4 0FQ
 UK: p) +44-1223-426-001, f) +44-871-971-1635
 DE: p) +49-6922-22340-60, f) +49-0800-58926-79
 IT: p) +39-02-4032-6786, f) +39-02-4032-6340
 FR: p) +33-1-76-77-45-30, f) +33-1-76-77-45-31
europe@novusbio.com

