

NBP1-19041**TMEM49 Antibody****Unit Size**

0.2 ml

Concentration

Lyoph

Storage

Store at 4C short term. Aliquot and store at -20C long term. Avoid freeze-thaw cycles.

Applications

WB, IHC, IHC-P

Species

Human, Mouse, Rat

Host

Rabbit

Clonality

Polyclonal

Purity

Whole antisera

Preservative

No Preservative

Specificity/Sensitivity

Reacts specifically with mouse 46 kDa protein

Immunogen

Synthetic peptide derived from Cter domain of TMEM49

Recommended Dilutions

Immunohistochemistry-Paraffin 1:50 to 1:500, Western Blot 1:200 to 1:2000, Immunohistochemistry

Buffer

Lyophilized Whole Rabbit antisera. Reconstitute in 200 ul of distilled water.

Uses

This antibody is useful for Immunohistochemistry-Paraffin, Western Blot

References

Ropolo A, Grasso D, Pardo R, et al. The pancreatitis-induced vacuole membrane protein 1 triggers autophagy in mammalian cells. J Biol Chem;282(51):37124-33. 2007 Dec 21. [PMID: 17940279]

ImagesThis product does not currently have an image. Earn rewards by submitting your image of this product. Submit a review with your image here: www.novusbio.com/NBP1-19041

Updated 3/9/2013 2.0

Limitations: This product is for research use only and is not approved for use in humans or in clinical diagnosis. Products are guaranteed for six months from the date of receipt except for peptides and proteins which are guaranteed for 3 months. For more information on our guarantee, please visit www.novusbio.com/guarantee.

Novus USA

8100 Southpark Way, A-8
 Littleton, CO 80120
 p) 888-506-6887
 p) 303-730-1950
 f) 303-730-1966
novus@novusbio.com

Novus Canada

461 North Service Road West,
 Unit B37
 Oakville, ON L6M 2V5
 p) 855-668-8722
 f) 905-827-6402
canada@novusbio.com

Novus Europe

12 Cambridge Science Park
 Cambridge, UK CB4 0FQ
 UK: p) +44-1223-426-001, f) +44-871-971-1635
 DE: p) +49-6922-22340-60, f) +49-0800-58926-79
 IT: p) +39-02-4032-6786, f) +39-02-4032-6340
 FR: p) +33-1-76-77-45-30, f) +33-1-76-77-45-31
europe@novusbio.com

