

NB7117

Goat anti-Rat IgG1 Antibody

Unit Size

1.0 mg

Concentration

1.0 mg/ml

Storage

Store at 4°C. Do not freeze.

Applications

WB, ELISA, ICC/IF, IHC, IHC-P

Species

Rat

Host

Goat

Clonality

Polyclonal

Isotype

IgG1

Purity

Immunogen affinity purified

Preservative

0.1% Sodium Azide

Specificity/Sensitivity

By immunoelectrophoresis and ELISA this reacts specifically with Rat IgG1. This may cross react with IgG1 from other species.

Immunogen

Rat IgG1

Recommended Dilutions

Immunohistochemistry 1:200 - 1:2000, Immunocytochemistry/Immunofluorescence 1:200 - 1:2000, Western Blot 1:1000-1:30000, ELISA 1:1000-1:30000 (Primary) 1:100-1:500 (For Coating Plates), Immunohistochemistry-Paraffin

Buffer

Phosphate Buffered Saline (PBS)

Images

This product does not currently have an image. Earn rewards by submitting your image of this product. Submit a review with your image here: www.novusbio.com/NB7117

Updated 3/9/2013 2.0

Limitations: This product is for research use only and is not approved for use in humans or in clinical diagnosis. Products are guaranteed for six months from the date of receipt except for peptides and proteins which are guaranteed for 3 months. **For more information on our guarantee, please visit www.novusbio.com/guarantee.**

Novus USA

8100 Southpark Way, A-8
 Littleton, CO 80120
 p) 888-506-6887
 p) 303-730-1950
 f) 303-730-1966
novus@novusbio.com

Novus Canada

461 North Service Road West,
 Unit B37
 Oakville, ON L6M 2V5
 p) 855-668-8722
 f) 905-827-6402
canada@novusbio.com

Novus Europe

12 Cambridge Science Park
 Cambridge, UK CB4 0FQ
 UK: p) +44-1223-426-001, f) +44-871-971-1635
 DE: p) +49-6922-22340-60, f) +49-0800-58926-79
 IT: p) +39-02-4032-6786, f) +39-02-4032-6340
 FR: p) +33-1-76-77-45-30, f) +33-1-76-77-45-31
europe@novusbio.com

