

NBC1-18391**14-3-3 gamma Protein****Unit Size**

0.1 mg

Concentration

1.0 mg/ml

Storage

Store at -80C. Avoid freeze-thaw cycles.

Applications

WB

Species

Human

Molecular Weight

28kDa

Purity

Protein

Preservative

No Preservative

Immunogen

14-3-3 gamma , 1-247aa, Human, Recombinant, E.coli (NP_036611).

Recommended Dilutions

Western Blot

Buffer

20mM Tris 7.5

Uses

Endotoxin level is < 1.0 EU per 1 microgram of protein (determined by LAL method). Purity is > 95% by SDS - PAGE.

Images

SDS-Page: 14-3-3 gamma Protein [NBC1-18391] -
 14-3-3 gamma, 28 kDa (247 aa), confirmed by
 MALDI-TOF with a purity of 95% by SDS - PAGE



Updated 3/9/2013 2.0

Limitations: This product is for research use only and is not approved for use in humans or in clinical diagnosis. Products are guaranteed for six months from the date of receipt except for peptides and proteins which are guaranteed for 3 months. **For more information on our guarantee, please visit www.novusbio.com/guarantee.**

Novus USA

8100 Southpark Way, A-8
 Littleton, CO 80120
 p) 888-506-6887
 p) 303-730-1950
 f) 303-730-1966
novus@novusbio.com

Novus Canada

461 North Service Road West,
 Unit B37
 Oakville, ON L6M 2V5
 p) 855-668-8722
 f) 905-827-6402
canada@novusbio.com

Novus Europe

12 Cambridge Science Park
 Cambridge, UK CB4 0FQ
 UK: p) +44-1223-426-001, f) +44-871-971-1635
 DE: p) +49-6922-22340-60, f) +49-0800-58926-79
 IT: p) +39-02-4032-6786, f) +39-02-4032-6340
 FR: p) +33-1-76-77-45-30, f) +33-1-76-77-45-31
europe@novusbio.com

