

NBC1-19070**OSTF1 Protein****Unit Size**

0.1 mg

Concentration

1.0 mg/ml

Storage

Store at -80C. Avoid freeze-thaw cycles.

Applications

ELISA, PAGE

Species

Human

Purity

Protein

Preservative

No Preservative

Immunogen

His tagged, Recombinant, E.coli: MSKPPPKPVK PGEGGQVKVF RALYTFEPRT
 PDELYFEEGD IYITDMSDT NWWKGTSGR TGLIPSNYYA EQAESIDNPL HEAAKRGNLS
 WLRECLDNRV GVNLGDKAGS TALYWACHGG HKDIVEMFLT QPNIELNQON
 KLGDTALHAA AWKGYADIVQ LFLAKGARTD LRNIEKKLAF DMATNAACAS LLKKKQGTDA
 VRTLSNAEDY LDDESDLEH HHHHH

Recommended Dilutions

ELISA
 SDS-Page

Buffer


20 mM Tris-HCl buffer (pH 8.0) containing 0.5mM DTT, 10% glycerol

Uses

This product is useful for ELISA and SDS-Page. The purity of this protein is > 90% by SDS - PAGE. This recombinant protein was expressed in E.Coli bacteria. The endotoxin levels of this protein have not yet been determined.

Images

Western Blot: OSTF1 Protein [NBC1-19070] - 25.1
 kDa (225 aa) on SDS - PAGE



Updated 3/9/2013 2.0

Limitations: This product is for research use only and is not approved for use in humans or in clinical diagnosis. Products are guaranteed for six months from the date of receipt except for peptides and proteins which are guaranteed for 3 months. **For more information on our guarantee, please visit www.novusbio.com/guarantee.**

Novus USA

8100 Southpark Way, A-8
 Littleton, CO 80120
 p) 888-506-6887
 p) 303-730-1950
 f) 303-730-1966
novus@novusbio.com

Novus Canada

461 North Service Road West,
 Unit B37
 Oakville, ON L6M 2V5
 p) 855-668-8722
 f) 905-827-6402
canada@novusbio.com

Novus Europe

12 Cambridge Science Park
 Cambridge, UK CB4 0FQ
 UK: p) +44-1223-426-001, f) +44-871-971-1635
 DE: p) +49-6922-22340-60, f) +49-0800-58926-79
 IT: p) +39-02-4032-6786, f) +39-02-4032-6340
 FR: p) +33-1-76-77-45-30, f) +33-1-76-77-45-31
europe@novusbio.com

