

NB600-1338**SOCS2 Antibody****Unit Size**

0.05 mg

Concentration

0.2 mg/ml

Storage

Store at 4C. Do not freeze.

Applications

WB, ELISA

Species

Human, Mouse, Rat

Molecular Weight

22kDa

Host

Rabbit

Clonality

Polyclonal

Purity

Immunogen affinity purified

Preservative

0.05% Sodium Azide

Specificity/Sensitivity

SOCS2

Immunogen

Synthetic peptide (PTRLKDYLEEYKFQV) corresponding to amino acids 184-198 of human, rat and mouse SOCS 2 (NP_003868).

Recommended Dilutions

ELISA 1:5000-1:20000

Western Blot 1:500-1:1000

Buffer

PBS

References

Inagaki, T., Lin, V., Goetz, R., et al. Inhibition of Growth Hormone Signaling by the Fasting-Induced Hormone FGF21. Cell Metabolism. ;(8)77-83. Jul-08. [PMID: 15837129]

Images

Western Blot: SOCS2 Antibody [NB600-1338] - Western blot analysis of the Hela cell lysate with the anti-SOCS2.



Updated 3/9/2013 2.0

Limitations: This product is for research use only and is not approved for use in humans or in clinical diagnosis. Products are guaranteed for six months from the date of receipt except for peptides and proteins which are guaranteed for 3 months. **For more information on our guarantee, please visit www.novusbio.com/guarantee.**

Novus USA

8100 Southpark Way, A-8
 Littleton, CO 80120
 p) 888-506-6887
 p) 303-730-1950
 f) 303-730-1966
novus@novusbio.com

Novus Canada

461 North Service Road West,
 Unit B37
 Oakville, ON L6M 2V5
 p) 855-668-8722
 f) 905-827-6402
canada@novusbio.com

Novus Europe

12 Cambridge Science Park
 Cambridge, UK CB4 0FQ
 UK: p) +44-1223-426-001, f) +44-871-971-1635
 DE: p) +49-6922-22340-60, f) +49-0800-58926-79
 IT: p) +39-02-4032-6786, f) +39-02-4032-6340
 FR: p) +33-1-76-77-45-30, f) +33-1-76-77-45-31
europe@novusbio.com

