

NB600-1398**Streptococcus B Antibody****Unit Size**

1.0 ml

Concentration

1.0 mg/ml

Storage

Store at 4C short term. Aliquot and store at -20C long term. Avoid freeze-thaw cycles.

Applications

ICC/IF

Species

Bacteria

Host

Rabbit

Clonality

Polyclonal

Purity

Protein A purified

Preservative

0.1% Sodium Azide

Specificity/Sensitivity

This targets a type specific carbohydrate of group B Streptococcus and does not react with other Strep groups.

Immunogen

Streptococci, group B.

Recommended Dilutions

Immunocytochemistry/Immunofluorescence

Buffer

Constituents: 0.01M PBS. pH 7.2. No stabilizing proteins have been added.

Uses

This antibody is useful for Immunofluorescence.

ImagesThis product does not currently have an image. Earn rewards by submitting your image of this product. Submit a review with your image here: www.novusbio.com/NB600-1398

Updated 3/9/2013 2.0

Limitations: This product is for research use only and is not approved for use in humans or in clinical diagnosis. Products are guaranteed for six months from the date of receipt except for peptides and proteins which are guaranteed for 3 months. **For more information on our guarantee, please visit www.novusbio.com/guarantee.**

Novus USA

8100 Southpark Way, A-8
 Littleton, CO 80120
 p) 888-506-6887
 p) 303-730-1950
 f) 303-730-1966
novus@novusbio.com

Novus Canada

461 North Service Road West,
 Unit B37
 Oakville, ON L6M 2V5
 p) 855-668-8722
 f) 905-827-6402
canada@novusbio.com

Novus Europe

12 Cambridge Science Park
 Cambridge, UK CB4 0FQ
 UK: p) +44-1223-426-001, f) +44-871-971-1635
 DE: p) +49-6922-22340-60, f) +49-0800-58926-79
 IT: p) +39-02-4032-6786, f) +39-02-4032-6340
 FR: p) +33-1-76-77-45-30, f) +33-1-76-77-45-31
europe@novusbio.com

