

NB820-59461**A-431 Whole Cell Lysate****Unit Size**

1.0 mg

Concentration

5.0 mg/ml

Storage

Store at -80C. Avoid freeze-thaw cycles.

Applications

WB, IP

Species

Human

Purity

Protein

Specificity/Sensitivity

Total Protein - Human Tumor Cell Line: A431

Recommended Dilutions

Immunoprecipitation, Western Blot

BufferHEPES, pH 7.9, MgCl₂, KCL, EDTA, Sucrose, Glycerol, Sodium deoxycholate, NP-40 and a cocktail of protease inhibitors.**Uses**

Western Blot, Immunoprecipitation, Electrophoresis, Enzymatic activity analysis, Protein-protein interaction, Tissue specific expression

ImagesThis product does not currently have an image. Earn rewards by submitting your image of this product. Submit a review with your image here: www.novusbio.com/NB820-59461

Updated 3/9/2013 2.0

Limitations: This product is for research use only and is not approved for use in humans or in clinical diagnosis. Products are guaranteed for six months from the date of receipt except for peptides and proteins which are guaranteed for 3 months. For more information on our guarantee, please visit www.novusbio.com/guarantee.

Novus USA

8100 Southpark Way, A-8
 Littleton, CO 80120
 p) 888-506-6887
 p) 303-730-1950
 f) 303-730-1966
novus@novusbio.com

Novus Canada

461 North Service Road West,
 Unit B37
 Oakville, ON L6M 2V5
 p) 855-668-8722
 f) 905-827-6402
canada@novusbio.com

Novus Europe

12 Cambridge Science Park
 Cambridge, UK CB4 0FQ
 UK: p) +44-1223-426-001, f) +44-871-971-1635
 DE: p) +49-6922-22340-60, f) +49-0800-58926-79
 IT: p) +39-02-4032-6786, f) +39-02-4032-6340
 FR: p) +33-1-76-77-45-30, f) +33-1-76-77-45-31
europe@novusbio.com

