

NB500-201G**Survivin Antibody [DyLight 488]****Unit Size**

0.05 ml

Concentration

1.0 mg/ml

Storage

Store at 4C in the dark.

Applications

WB, ICC/IF, IHC, IHC-P, IP

Species

Human, Mouse, Rat, Canine, Feline

Host

Rabbit

Clonality

Polyclonal

Conjugate

DyLight 488

Purity

Affinity purified

Preservative

No Preservative

Marker

Astrocyte Marker

Specificity/Sensitivity

This is specific for survivin.

Immunogen

Full-length recombinant human survivin.

Recommended Dilutions

Immunoprecipitation, Western Blot, Immunohistochemistry-Paraffin, Immunocytochemistry/Immunofluorescence, Immunohistochemistry

Buffer

50mM sodium borate

Uses

By Western blot, this antibody recognizes a band at ~16.5 kDa representing survivin. Immunohistochemistry with cytoplasmic and nuclear detection of survivin can be achieved using formalin-fixed paraffin-embedded tissue sections with prior antigen retrieval (pressure cooking).

Images

This product does not currently have an image. Earn rewards by submitting your image of this product. Submit a review with your image here: www.novusbio.com/NB500-201G

Updated 3/9/2013 2.0

Limitations: This product is for research use only and is not approved for use in humans or in clinical diagnosis. Products are guaranteed for six months from the date of receipt except for peptides and proteins which are guaranteed for 3 months. **For more information on our guarantee, please visit www.novusbio.com/guarantee.**

Novus USA

8100 Southpark Way, A-8
 Littleton, CO 80120
 p) 888-506-6887
 p) 303-730-1950
 f) 303-730-1966
novus@novusbio.com

Novus Canada

461 North Service Road West,
 Unit B37
 Oakville, ON L6M 2V5
 p) 855-668-8722
 f) 905-827-6402
canada@novusbio.com

Novus Europe

12 Cambridge Science Park
 Cambridge, UK CB4 0FQ
 UK: p) +44-1223-426-001, f) +44-871-971-1635
 DE: p) +49-6922-22340-60, f) +49-0800-58926-79
 IT: p) +39-02-4032-6786, f) +39-02-4032-6340
 FR: p) +33-1-76-77-45-30, f) +33-1-76-77-45-31
europe@novusbio.com

