

NB600-532G**Beta Actin Antibody [DyLight 488]****Unit Size**

0.1 mg

Concentration

1.0 mg/ml

Storage

Store at 4°C in the dark.

Applications

WB, IP

Species

Human, Mouse

Host

Rabbit

Clonality

Polyclonal

Conjugate

DyLight 488

Purity

Immunogen affinity purified

Preservative

No Preservative

Specificity/Sensitivity

Detects a single clean band at 40kD representing actin.

Immunogen

The epitope recognized by this antibody maps to the N-terminus of human Beta-actin using the numbering given in Swiss-Prot entry P60709 (GeneID 60).

Recommended Dilutions

Immunoprecipitation 2-5 ug/mg, Western Blot 1:5000-1:15000

Buffer

PBS

Uses

This antibody can be used in WB where a 40 kDa band is detected in HeLa whole cell lysate and mouse NIH3T3 cells. Optimal dilutions should be determined by the end user.

ImagesThis product does not currently have an image. Earn rewards by submitting your image of this product. Submit a review with your image here: www.novusbio.com/NB600-532G

Updated 3/9/2013 2.0

Limitations: This product is for research use only and is not approved for use in humans or in clinical diagnosis. Products are guaranteed for six months from the date of receipt except for peptides and proteins which are guaranteed for 3 months. For more information on our guarantee, please visit www.novusbio.com/guarantee.

Novus USA

8100 Southpark Way, A-8
 Littleton, CO 80120
 p) 888-506-6887
 p) 303-730-1950
 f) 303-730-1966
novus@novusbio.com

Novus Canada

461 North Service Road West,
 Unit B37
 Oakville, ON L6M 2V5
 p) 855-668-8722
 f) 905-827-6402
canada@novusbio.com

Novus Europe

12 Cambridge Science Park
 Cambridge, UK CB4 0FQ
 UK: p) +44-1223-426-001, f) +44-871-971-1635
 DE: p) +49-6922-22340-60, f) +49-0800-58926-79
 IT: p) +39-02-4032-6786, f) +39-02-4032-6340
 FR: p) +33-1-76-77-45-30, f) +33-1-76-77-45-31
europe@novusbio.com

