



NB400-144PEP

CD36 Peptide

Orders: orders@novusbio.com

Support: technical@novusbio.com

Web: www.novusbio.com

Protocols, Publications, Related Products, Reviews and more:

www.novusbio.com/NB400-144PEP

Unit Size

0.05 mg

Concentration

1.0 mg/ml

Storage

Store at -80C. Avoid freeze-thaw cycles.

Preservative

No Preservative

Specificity/Sensitivity

This peptide is specific for NB400-144 only.

Buffer

Peptide dissolved in dH₂O. Contains no BSA.

Uses

Used as a blocking peptide for NB 400-144

Images

This product does not currently have an image. Earn rewards by submitting your image of this product. Submit a review with your image here: www.novusbio.com/NB400-144PEP

Updated 3/9/2013 2.0

Limitations: This product is for research use only and is not approved for use in humans or in clinical diagnosis. Products are guaranteed for six months from the date of receipt except for peptides and proteins which are guaranteed for 3 months. For more information on our guarantee, please visit www.novusbio.com/guarantee.

Novus USA

8100 Southpark Way, A-8
Littleton, CO 80120
p) 888-506-6887
p) 303-730-1950
f) 303-730-1966
novus@novusbio.com

Novus Canada

461 North Service Road West,
Unit B37
Oakville, ON L6M 2V5
p) 855-668-8722
f) 905-827-6402
canada@novusbio.com

Novus Europe

12 Cambridge Science Park
Cambridge, UK CB4 0FQ
UK: p) +44-1223-426-001, f) +44-871-971-1635
DE: p) +49-6922-22340-60, f) +49-0800-58926-79
IT: p) +39-02-4032-6786, f) +39-02-4032-6340
FR: p) +33-1-76-77-45-30, f) +33-1-76-77-45-31
europe@novusbio.com

