

NB120-6521**Donkey anti-Goat IgG, Fab2, H/L Chains Antibody [FITC]****Unit Size**

1 mg

Concentration

Lyophil

Storage

Store at 4°C short term. Aliquot and store at -20°C long term. Avoid freeze-thaw cycles.

Applications

FLISA, ICC/IF

Species

Goat

Host

Donkey

Clonality

Polyclonal

Isotype

IgG

Conjugate

FITC

Purity

Immunogen affinity purified

Preservative

0.01% Sodium Azide

Specificity/Sensitivity

Assay by immunoelectrophoresis resulted in a single precipitin arc against anti-Fluorescein and anti-Donkey Serum. No reaction was observed against anti-Pepsin or anti-Donkey IgG F(c).

Immunogen

Goat IgG whole molecule

Recommended Dilutions

Fluorophore-linked immunosorbent assay 1:10000 - 1:50000, Immunocytochemistry/Immunofluorescence 1:1000 - 1:5000

Buffer

0.02 M Potassium Phosphate, 0.15 M Sodium Chloride, pH 7.2, 10 mg/ml Bovine Serum Albumin (BSA). Lyophilized. Reconstitute in 1.0mL of DI Water.

Uses

Suitable for immunomicroscopy and flow cytometry as well as other antibody based fluorescent assays requiring extremely low background levels, absence of F mediated binding, lot-to-lot consistency, high titer and specificity.

ImagesThis product does not currently have an image. Earn rewards by submitting your image of this product. Submit a review with your image here: www.novusbio.com/NB120-6521

Updated 3/9/2013 2.0

Limitations: This product is for research use only and is not approved for use in humans or in clinical diagnosis. Products are guaranteed for six months from the date of receipt except for peptides and proteins which are guaranteed for 3 months. **For more information on our guarantee, please visit www.novusbio.com/guarantee.**

Novus USA

8100 Southpark Way, A-8
 Littleton, CO 80120
 p) 888-506-6887
 p) 303-730-1950
 f) 303-730-1966
novus@novusbio.com

Novus Canada

461 North Service Road West,
 Unit B37
 Oakville, ON L6M 2V5
 p) 855-668-8722
 f) 905-827-6402
canada@novusbio.com

Novus Europe

12 Cambridge Science Park
 Cambridge, UK CB4 0FQ
 UK: p) +44-1223-426-001, f) +44-871-971-1635
 DE: p) +49-6922-22340-60, f) +49-0800-58926-79
 IT: p) +39-02-4032-6786, f) +39-02-4032-6340
 FR: p) +33-1-76-77-45-30, f) +33-1-76-77-45-31
europe@novusbio.com

