

NB120-6948**Donkey anti-Goat IgG Antibody [Cy2]****Unit Size**

0.2 mg

Concentration

Please see the vial label for concentration.

Storage

Store at 4C short term. Aliquot and store at -20C long term. Avoid freeze-thaw cycles.

Applications

FLOW, ICC/IF, IHC, IHC-Fr, IHC-P

Species

Goat

Host

Donkey

Clonality

Polyclonal

Isotype

IgG

Conjugate

Cy2

Purity

Immunogen affinity purified

Preservative

0.01% Sodium Azide

Specificity/Sensitivity

Assay by immunoelectrophoresis resulted in a single precipitin arc against anti-Donkey Serum, Goat IgG and Goat Serum. No reaction was observed against Chicken, Guinea Pig, Hamster, Horse, Mouse, Rabbit and Rat Serum Proteins.

Immunogen

Full length native Goat IgG (purified).

Recommended Dilutions

Flow Cytometry, Immunohistochemistry-Paraffin, Immunohistochemistry-Frozen, Immunocytochemistry/Immunofluorescence, Immunohistochemistry

Buffer

Buffer: 0.02 M Potassium Phosphate, 0.15 M Sodium Chloride, pH 7.2 Stabilizer: 10 mg/ml Bovine Serum

Uses

Flow Cytometry Use at an assay dependant concentration. ICC: Use at an assay dependant concentration. IF: Use at an assay dependant concentration. IHC-P: Use at an assay dependant concentration. IHC-Fr: Use at an assay dependant concentration.

ImagesThis product does not currently have an image. Earn rewards by submitting your image of this product. Submit a review with your image here: www.novusbio.com/NB120-6948

Updated 3/9/2013 2.0

Limitations: This product is for research use only and is not approved for use in humans or in clinical diagnosis. Products are guaranteed for six months from the date of receipt except for peptides and proteins which are guaranteed for 3 months. **For more information on our guarantee, please visit www.novusbio.com/guarantee.**

Novus USA
 8100 Southpark Way, A-8
 Littleton, CO 80120
 p) 888-506-6887
 p) 303-730-1950
 f) 303-730-1966
novus@novusbio.com
Novus Canada
 461 North Service Road West,
 Unit B37
 Oakville, ON L6M 2V5
 p) 855-668-8722
 f) 905-827-6402
canada@novusbio.com
Novus Europe
 12 Cambridge Science Park
 Cambridge, UK CB4 0FQ
 UK: p) +44-1223-426-001, f) +44-871-971-1635
 DE: p) +49-6922-22340-60, f) +49-0800-58926-79
 IT: p) +39-02-4032-6786, f) +39-02-4032-6340
 FR: p) +33-1-76-77-45-30, f) +33-1-76-77-45-31
europe@novusbio.com
