

**NB120-7061****Donkey anti-Mouse IgG Antibody [HRP]****Unit Size**

0.2 mg

**Concentration**

1.0 mg/ml

**Storage**

Store at 4°C short term. Aliquot and store at -20°C long term. Avoid freeze-thaw cycles.

**Applications**

WB, ELISA, IHC, IHC-P

**Species**

Mouse

**Host**

Donkey

**Clonality**

Polyclonal

**Isotype**

IgG

**Conjugate**

HRP

**Purity**

IgG purified

**Preservative**

0.01% Gentamicin Sulfate

**Specificity/Sensitivity**

Assay by immunoelectrophoresis resulted in a single precipitin arc against anti-Peroxidase, anti-Donkey Serum, Mouse IgG and Mouse Serum. No reaction was observed against Bovine, Chicken, Goat, Guinea Pig, Hamster, Horse, Human, Rabbit, Rat and Sheep Serum Proteins.

**Immunogen**

Full length native mouse IgG (purified).

**Recommended Dilutions**

ELISA 1:180000, Immunohistochemistry 1:1000 - 1:5000, Western Blot 1:2000 - 1:20000, Immunohistochemistry-Paraffin

**Buffer**

0.02 M Potassium Phosphate, 0.15 M Sodium Chloride, pH 7.2, 10 mg/ml BSA (Immunoglobulin and Protease free). DO NOT add Sodium Azide!

**References**

Karman J, Gumlaw NK, Zhang J, Jiang JL, Cheng SH, Zhu Y. Proteasome Inhibition Is Partially Effective in Attenuating Pre-Existing Immunity against Recombinant Adeno-Associated Viral Vectors. PLoS One;7(4). 2012. [PMID: 22514654] (ELISA, Mouse

**Images**

This product does not currently have an image. Earn rewards by submitting your image of this product. Submit a review with your image here: [www.novusbio.com/NB120-7061](http://www.novusbio.com/NB120-7061)

Updated 3/9/2013 2.0

**Limitations:** This product is for research use only and is not approved for use in humans or in clinical diagnosis. Products are guaranteed for six months from the date of receipt except for peptides and proteins which are guaranteed for 3 months. **For more information on our guarantee, please visit [www.novusbio.com/guarantee](http://www.novusbio.com/guarantee).**

**Novus USA**

8100 Southpark Way, A-8  
 Littleton, CO 80120  
 p) 888-506-6887  
 p) 303-730-1950  
 f) 303-730-1966  
[novus@novusbio.com](mailto:novus@novusbio.com)

**Novus Canada**

461 North Service Road West,  
 Unit B37  
 Oakville, ON L6M 2V5  
 p) 855-668-8722  
 f) 905-827-6402  
[canada@novusbio.com](mailto:canada@novusbio.com)

**Novus Europe**

12 Cambridge Science Park  
 Cambridge, UK CB4 0FQ  
 UK: p) +44-1223-426-001, f) +44-871-971-1635  
 DE: p) +49-6922-22340-60, f) +49-0800-58926-79  
 IT: p) +39-02-4032-6786, f) +39-02-4032-6340  
 FR: p) +33-1-76-77-45-30, f) +33-1-76-77-45-31  
[europe@novusbio.com](mailto:europe@novusbio.com)

