

NB200-147**TSKS Antibody****Unit Size**

0.1 ml

Concentration

Please see the vial label for concentration.

Storage

Store at 4C short term. Aliquot and store at -20C long term. Avoid freeze-thaw cycles.

Applications

WB, ELISA, IHC, IHC-Fr, IHC-P

Species

Human

Host

Rabbit

Clonality

Polyclonal

Purity

IgG purified

Preservative

0.02% Sodium Azide

Specificity/Sensitivity

Reacts with residues 577-592 of the human TSKS protein.

Immunogen

Residues 577-592 of the human TSKS protein

Recommended Dilutions

ELISA, Western Blot, Immunohistochemistry-Frozen, Immunohistochemistry-Paraffin, Immunohistochemistry

Buffer

PBS

Uses

ELISA, Western Blot

ImagesThis product does not currently have an image. Earn rewards by submitting your image of this product. Submit a review with your image here: www.novusbio.com/NB200-147

Updated 3/9/2013 2.0

Limitations: This product is for research use only and is not approved for use in humans or in clinical diagnosis. Products are guaranteed for six months from the date of receipt except for peptides and proteins which are guaranteed for 3 months. **For more information on our guarantee, please visit www.novusbio.com/guarantee.**

Novus USA

8100 Southpark Way, A-8
 Littleton, CO 80120
 p) 888-506-6887
 p) 303-730-1950
 f) 303-730-1966
novus@novusbio.com

Novus Canada

461 North Service Road West,
 Unit B37
 Oakville, ON L6M 2V5
 p) 855-668-8722
 f) 905-827-6402
canada@novusbio.com

Novus Europe

12 Cambridge Science Park
 Cambridge, UK CB4 0FQ
 UK: p) +44-1223-426-001, f) +44-871-971-1635
 DE: p) +49-6922-22340-60, f) +49-0800-58926-79
 IT: p) +39-02-4032-6786, f) +39-02-4032-6340
 FR: p) +33-1-76-77-45-30, f) +33-1-76-77-45-31
europe@novusbio.com

