

NB110-81601H**TRPM2 Antibody [HRP]****Unit Size**

0.1 ml

Concentration

1.25 mg/ml

Storage

Store at 4C in the dark.

Applications

WB, IHC

Species

Mouse, Rat

Host

Rabbit

Clonality

Polyclonal

Conjugate

HRP

Purity

Peptide affinity purified

Preservative

No Preservative

Specificity/Sensitivity

This is specific for isoform 1, or the long isoform (TRPM2-L), of TRPM2.

Immunogen

Synthetic peptide made to a C-terminal portion of the rat protein (within residues 1430-1508). [Swiss-Prot# Q5G856]

Recommended Dilutions

immunohistochemistry 1:200, Western Blot 1:500-1:1000,

Buffer

PBS

Uses

This antibody is useful for Western blot, where a band is seen ~181 kDa. This antibody is also useful for immunohistochemistry.

ImagesThis product does not currently have an image. Earn rewards by submitting your image of this product. Submit a review with your image here: www.novusbio.com/NB110-81601H

Updated 3/9/2013 2.0

Limitations: This product is for research use only and is not approved for use in humans or in clinical diagnosis. Products are guaranteed for six months from the date of receipt except for peptides and proteins which are guaranteed for 3 months. For more information on our guarantee, please visit www.novusbio.com/guarantee.

Novus USA

8100 Southpark Way, A-8
 Littleton, CO 80120
 p) 888-506-6887
 p) 303-730-1950
 f) 303-730-1966
novus@novusbio.com

Novus Canada

461 North Service Road West,
 Unit B37
 Oakville, ON L6M 2V5
 p) 855-668-8722
 f) 905-827-6402
canada@novusbio.com

Novus Europe

12 Cambridge Science Park
 Cambridge, UK CB4 0FQ
 UK: p) +44-1223-426-001, f) +44-871-971-1635
 DE: p) +49-6922-22340-60, f) +49-0800-58926-79
 IT: p) +39-02-4032-6786, f) +39-02-4032-6340
 FR: p) +33-1-76-77-45-30, f) +33-1-76-77-45-31
europe@novusbio.com

