

NB110-83982**BCL2L1 Antibody****Unit Size**

0.1 ml

Concentration

1 mg/ml

Storage

Store at 4C. Do not freeze.

Applications

WB

Species

Human, Canine, Feline, Porcine, Sheep

Molecular Weight

26kDa

Host

Rabbit

Clonality

Polyclonal

Purity

Immunogen affinity purified

Preservative

0.1% Sodium Azide

Specificity/Sensitivity

There are three known isoforms of Bcl-X; Bcl-X(S), Bcl-X(beta), and Bcl-X(L). The immunogen used to create this has 100% identity to all three isoforms.

Immunogen

Synthetic peptide made to an N-terminal portion of human BCL2L1 (within residues 30-70). [Swiss-Prot# Q07817]

Recommended Dilutions

Western Blot 2.0 mg/ml

Buffer

Tris-citrate/phosphate, pH 7-8

Uses

This BCL2L1 antibody is useful for Western blot, where a band is seen ~26 kDa.

Images

Detection of Bcl-x in A431 whole cell extracts using NB110-83982.



Updated 3/9/2013 2.0

Limitations: This product is for research use only and is not approved for use in humans or in clinical diagnosis. Products are guaranteed for six months from the date of receipt except for peptides and proteins which are guaranteed for 3 months. **For more information on our guarantee, please visit www.novusbio.com/guarantee.**

Novus USA

8100 Southpark Way, A-8
 Littleton, CO 80120
 p) 888-506-6887
 p) 303-730-1950
 f) 303-730-1966
novus@novusbio.com

Novus Canada

461 North Service Road West,
 Unit B37
 Oakville, ON L6M 2V5
 p) 855-668-8722
 f) 905-827-6402
canada@novusbio.com

Novus Europe

12 Cambridge Science Park
 Cambridge, UK CB4 0FQ
 UK: p) +44-1223-426-001, f) +44-871-971-1635
 DE: p) +49-6922-22340-60, f) +49-0800-58926-79
 IT: p) +39-02-4032-6786, f) +39-02-4032-6340
 FR: p) +33-1-76-77-45-30, f) +33-1-76-77-45-31
europe@novusbio.com

