

NB110-55376H**TARDBP Antibody [HRP]****Unit Size**

0.1 ml

Concentration

1.0 mg/ml

Storage

Store at 4C in the dark.

Applications

WB

Species

Human, Mouse, Chicken, Primate, Xenopus, Zebrafish

Host

Rabbit

Clonality

Polyclonal

Conjugate

HRP

Purity

Immunogen affinity purified

Preservative

No Preservative

Specificity/Sensitivity

TARDBP

Immunogen

A synthetic peptide to a C-terminal region [within residues 350-414] of the human TARDBP protein. [Swiss-Prot# Q13148]

Recommended Dilutions

Western Blot 0.5 to 2.0 ug/ ml

Buffer

PBS

Uses

This antibody can be used for Western blot analysis where a band is seen at ~45 kDa, representing the human TARDBP protein.

ImagesThis product does not currently have an image. Earn rewards by submitting your image of this product. Submit a review with your image here: www.novusbio.com/NB110-55376H

Updated 3/9/2013 2.0

Limitations: This product is for research use only and is not approved for use in humans or in clinical diagnosis. Products are guaranteed for six months from the date of receipt except for peptides and proteins which are guaranteed for 3 months. For more information on our guarantee, please visit www.novusbio.com/guarantee.

Novus USA

8100 Southpark Way, A-8
 Littleton, CO 80120
 p) 888-506-6887
 p) 303-730-1950
 f) 303-730-1966
novus@novusbio.com

Novus Canada

461 North Service Road West,
 Unit B37
 Oakville, ON L6M 2V5
 p) 855-668-8722
 f) 905-827-6402
canada@novusbio.com

Novus Europe

12 Cambridge Science Park
 Cambridge, UK CB4 0FQ
 UK: p) +44-1223-426-001, f) +44-871-971-1635
 DE: p) +49-6922-22340-60, f) +49-0800-58926-79
 IT: p) +39-02-4032-6786, f) +39-02-4032-6340
 FR: p) +33-1-76-77-45-30, f) +33-1-76-77-45-31
europe@novusbio.com

