

NB110-60993**MMP14 Antibody (MM0027-9E10)****Unit Size**

0.1 mg

Concentration

lyoph

Storage

Store at 4C short term. Aliquot and store at -20C long term. Avoid freeze-thaw cycles.

Applications

WB, IHC, IHC-P

Species

Human

Host

Mouse

Clonality

Monoclonal

Isotype

IgG1

Purity

Protein G purified

Preservative

No Preservative

Specificity/Sensitivity

This antibody recognizes human MMP-14 in western blot without cross reactivity with human MMP-1-13, and MMP14-15.

Immunogen

This antibody was produced from a hybridoma (mouse myeloma fused with spleen cells from a mouse immunized with purified human recombinant MMP-14).

Recommended Dilutions

Western Blot 1:400-1:800, Immunohistochemistry-Paraffin 1:50-200, Immunohistochemistry

Buffer

Lyophilized - Reconstitute the antibody with 500 ul sterile PBS and the final concentration is 200ug/ml.

Uses

This product is useful in Western Blot and Immunohistochemistry (Paraffin).

Images

Immunohistochemistry-Paraffin: MMP14 Antibody (MM0027-9E10) [NB110-60993] - Human placenta (formalin fixed and paraffin embedded) section is subjected to IHC.



Updated 3/9/2013 2.0

Limitations: This product is for research use only and is not approved for use in humans or in clinical diagnosis. Products are guaranteed for six months from the date of receipt except for peptides and proteins which are guaranteed for 3 months. For more information on our guarantee, please visit www.novusbio.com/guarantee.

Novus USA

8100 Southpark Way, A-8
 Littleton, CO 80120
 p) 888-506-6887
 p) 303-730-1950
 f) 303-730-1966
novus@novusbio.com

Novus Canada

461 North Service Road West,
 Unit B37
 Oakville, ON L6M 2V5
 p) 855-668-8722
 f) 905-827-6402
canada@novusbio.com

Novus Europe

12 Cambridge Science Park
 Cambridge, UK CB4 0FQ
 UK: p) +44-1223-426-001, f) +44-871-971-1635
 DE: p) +49-6922-22340-60, f) +49-0800-58926-79
 IT: p) +39-02-4032-6786, f) +39-02-4032-6340
 FR: p) +33-1-76-77-45-30, f) +33-1-76-77-45-31
europe@novusbio.com

