

NB100-94377**TLR7 Antibody****Unit Size**

0.1 mg

Concentration

1.0 mg/ml

Storage

Store at 4C. Do not freeze.

Applications

WB

Species

Human, Mouse

Host

Rabbit

Clonality

Polyclonal

Purity

IgG purified

Preservative

0.02% Sodium Azide

Immunogen

Rabbit anti-TLR7 (IN) polyclonal antibody was raised against a peptide corresponding to 14 amino acids near the middle of mouse TLR7 (GenBank accession no. NP_573474).

Recommended Dilutions

Western Blot 0.5-2 ug/ml

Buffer

PBS

Uses

This polyclonal antibody can be used for detection of TLR7 by Western blot at 0.5 to 2 ug/ml. It is human and mouse reactive.

Images

Western Blot: TLR7 Antibody [NB100-94377] -
 Western blot analysis of TLR7 in Daudi cell lysates
 with anti-TLR7 (IN) at (A) 0.5, (B) 1, and (C) 2 ug/ml.



Updated 3/9/2013 2.0

Limitations: This product is for research use only and is not approved for use in humans or in clinical diagnosis. Products are guaranteed for six months from the date of receipt except for peptides and proteins which are guaranteed for 3 months. **For more information on our guarantee, please visit www.novusbio.com/guarantee.**

Novus USA

8100 Southpark Way, A-8
 Littleton, CO 80120
 p) 888-506-6887
 p) 303-730-1950
 f) 303-730-1966
novus@novusbio.com

Novus Canada

461 North Service Road West,
 Unit B37
 Oakville, ON L6M 2V5
 p) 855-668-8722
 f) 905-827-6402
canada@novusbio.com

Novus Europe

12 Cambridge Science Park
 Cambridge, UK CB4 0FQ
 UK: p) +44-1223-426-001, f) +44-871-971-1635
 DE: p) +49-6922-22340-60, f) +49-0800-58926-79
 IT: p) +39-02-4032-6786, f) +39-02-4032-6340
 FR: p) +33-1-76-77-45-30, f) +33-1-76-77-45-31
europe@novusbio.com

