

**NB110-2502****Bacillus anthracis Antibody****Unit Size**

0.2 mg

**Concentration**

1.5 mg/ml

**Storage**

Store at 4C. Do not freeze.

**Applications**

WB, ELISA

**Species**

Bacteria

**Host**

Rabbit

**Clonality**

Polyclonal

**Purity**

Protein A purified

**Preservative**

0.1% Sodium Azide

**Specificity/Sensitivity**Spore antigen of *Bacillus anthracis*. Cross-reaction with extracts from spore and vegetative cells of other *Bacillus* species is less than 5%.**Immunogen**

Spore extract (MW 90 kD)

**Recommended Dilutions**

Western Blot

ELISA

**Buffer**

Phosphate buffered saline, pH 7.2 with 0.005% merthiolate

**Uses**

This antibody is useful for ELISA and Western Blot.

**Images**This product does not currently have an image. Earn rewards by submitting your image of this product. Submit a review with your image here: [www.novusbio.com/NB110-2502](http://www.novusbio.com/NB110-2502)

Updated 3/9/2013 2.0

**Limitations:** This product is for research use only and is not approved for use in humans or in clinical diagnosis. Products are guaranteed for six months from the date of receipt except for peptides and proteins which are guaranteed for 3 months. **For more information on our guarantee, please visit [www.novusbio.com/guarantee](http://www.novusbio.com/guarantee).**

**Novus USA**

8100 Southpark Way, A-8  
 Littleton, CO 80120  
 p) 888-506-6887  
 p) 303-730-1950  
 f) 303-730-1966  
[novus@novusbio.com](mailto:novus@novusbio.com)

**Novus Canada**

461 North Service Road West,  
 Unit B37  
 Oakville, ON L6M 2V5  
 p) 855-668-8722  
 f) 905-827-6402  
[canada@novusbio.com](mailto:canada@novusbio.com)

**Novus Europe**

12 Cambridge Science Park  
 Cambridge, UK CB4 0FQ  
 UK: p) +44-1223-426-001, f) +44-871-971-1635  
 DE: p) +49-6922-22340-60, f) +49-0800-58926-79  
 IT: p) +39-02-4032-6786, f) +39-02-4032-6340  
 FR: p) +33-1-76-77-45-30, f) +33-1-76-77-45-31  
[europe@novusbio.com](mailto:europe@novusbio.com)

