

NB100-73230**Yersinia Pestis V Antigen Antibody (Va68)****Unit Size**

0.2 mg

Concentration

Please see the vial label for concentration.

Storage

Store at 4C. Do not freeze.

Applications

WB, ELISA

Species

Bacteria

Host

Mouse

Clonality

Monoclonal

Isotype

IgG1

Purity

Protein G purified

Preservative

0.1% Sodium Azide

Specificity/Sensitivity

Y. pestis, V antigen

Immunogen

Y. pestis, V antigen

Recommended Dilutions

ELISA

Western Blot

Buffer

PBS, pH 7.4

Uses

ELISA and Western blot

Images

This product does not currently have an image. Earn rewards by submitting your image of this product. Submit a review with your image here: www.novusbio.com/NB100-73230

Updated 3/9/2013 2.0

Limitations: This product is for research use only and is not approved for use in humans or in clinical diagnosis. Products are guaranteed for six months from the date of receipt except for peptides and proteins which are guaranteed for 3 months. **For more information on our guarantee, please visit www.novusbio.com/guarantee.**

Novus USA

8100 Southpark Way, A-8
 Littleton, CO 80120
 p) 888-506-6887
 p) 303-730-1950
 f) 303-730-1966
novus@novusbio.com

Novus Canada

461 North Service Road West,
 Unit B37
 Oakville, ON L6M 2V5
 p) 855-668-8722
 f) 905-827-6402
canada@novusbio.com

Novus Europe

12 Cambridge Science Park
 Cambridge, UK CB4 0FQ
 UK: p) +44-1223-426-001, f) +44-871-971-1635
 DE: p) +49-6922-22340-60, f) +49-0800-58926-79
 IT: p) +39-02-4032-6786, f) +39-02-4032-6340
 FR: p) +33-1-76-77-45-30, f) +33-1-76-77-45-31
europe@novusbio.com

