

NB100-74407**ECM29 Antibody****Unit Size**

0.1 mg

Concentration

Concentrations vary lot to lot. See vial label for concentration.

Storage

Store at -20C. Avoid freeze-thaw cycles.

Applications

WB, ICC/IF, IHC, IHC-P

Species

Human, Mouse

Host

Rabbit

Clonality

Polyclonal

Purity

Whole antisera

Preservative

0.05% Sodium Azide

Specificity/Sensitivity

Ecm29

Immunogen

Synthetic peptide corresponding to the C-terminal residues R(a.a. 1821) P E L Q E K A A L L K K T L E N L E(a.a. 1839) of human Ecm29.

Recommended Dilutions

Western Blot 1:200, Immunohistochemistry-Paraffin, Immunocytochemistry/Immunofluorescence 1:200, Immunohistochemistry

Uses

Western Blot and Immunofluorescence. In WB analysis of HeLa cell extracts this antibody detects an approx. 205 kDa protein representing Ecm29.

Images

Western Blot: ECM29 Antibody [NB100-74407] - Figure 1 shows a Western blot of Ecm29 in HeLa cells using NB100-74407. Figure 2 shows immunofluorescent staining of Ecm29 in HeLa cells using NB100-74407.



Updated 3/9/2013 2.0

Limitations: This product is for research use only and is not approved for use in humans or in clinical diagnosis. Products are guaranteed for six months from the date of receipt except for peptides and proteins which are guaranteed for 3 months. **For more information on our guarantee, please visit www.novusbio.com/guarantee.**

Novus USA

8100 Southpark Way, A-8
 Littleton, CO 80120
 p) 888-506-6887
 p) 303-730-1950
 f) 303-730-1966
novus@novusbio.com

Novus Canada

461 North Service Road West,
 Unit B37
 Oakville, ON L6M 2V5
 p) 855-668-8722
 f) 905-827-6402
canada@novusbio.com

Novus Europe

12 Cambridge Science Park
 Cambridge, UK CB4 0FQ
 UK: p) +44-1223-426-001, f) +44-871-971-1635
 DE: p) +49-6922-22340-60, f) +49-0800-58926-79
 IT: p) +39-02-4032-6786, f) +39-02-4032-6340
 FR: p) +33-1-76-77-45-30, f) +33-1-76-77-45-31
europe@novusbio.com

