

NB100-74543**SREBP2 Antibody****Unit Size**

0.1 mg

Concentration

Concentrations vary lot to lot. See vial label for concentration.

Storage

Store at -20°C. Avoid freeze-thaw cycles.

Applications

WB

Species

Mouse, Rat

Host

Rabbit

Clonality

Polyclonal

Purity

Immunogen affinity purified

Preservative

0.05% Sodium Azide

Specificity/Sensitivity

SREBP2

Immunogen

Synthetic peptide corresponding to residues A(a.a. 843) I S W L Q G D D A A V R S H(a.a. 857) of rat SREBP 2.

Recommended Dilutions

Western Blot 1:500-1:1500

Buffer

PBS containing 1 mg/ml BSA

Uses

This antibody is useful for Western Blot.

References (more available at www.novusbio.com/NB100-74543)

Duan Y, Chen Y, Hu W et al. Peroxisome Proliferator-activated Receptor Activation by Ligands and Dephosphorylation Induces Proprotein Convertase Subtilisin Kexin Type 9 and Low Density Lipoprotein Receptor Expression J Biol Chem 2012 Jul 6 [PMID: 22593575] (WB, Human, Mouse)

Images

This product does not currently have an image. Earn rewards by submitting your image of this product. Submit a review with your image here: www.novusbio.com/NB100-74543

Updated 3/9/2013 2.0

Limitations: This product is for research use only and is not approved for use in humans or in clinical diagnosis. Products are guaranteed for six months from the date of receipt except for peptides and proteins which are guaranteed for 3 months. **For more information on our guarantee, please visit www.novusbio.com/guarantee.**

Novus USA

8100 Southpark Way, A-8
 Littleton, CO 80120
 p) 888-506-6887
 p) 303-730-1950
 f) 303-730-1966
novus@novusbio.com

Novus Canada

461 North Service Road West,
 Unit B37
 Oakville, ON L6M 2V5
 p) 855-668-8722
 f) 905-827-6402
canada@novusbio.com

Novus Europe

12 Cambridge Science Park
 Cambridge, UK CB4 0FQ
 UK: p) +44-1223-426-001, f) +44-871-971-1635
 DE: p) +49-6922-22340-60, f) +49-0800-58926-79
 IT: p) +39-02-4032-6786, f) +39-02-4032-6340
 FR: p) +33-1-76-77-45-30, f) +33-1-76-77-45-31
europe@novusbio.com

