

NB100-74564**Vimentin Antibody (J144)****Unit Size**

0.2 ml

Concentration

Concentrations vary lot to lot. See vial label for concentration.

Storage

Store at -20C. Avoid freeze-thaw cycles.

Applications

WB, ICC/IF, IHC, IHC-P

Species

Human, Mouse, Rat

Host

Mouse

Clonality

Monoclonal

Isotype

IgM

Purity

Ascites

Preservative

0.05% Sodium Azide

Marker

Neuronal Stem Cell Marker, Cytoskeleton-Intermediate Filaments Marker

Updated 3/9/2013 2.0

Immunogen

Human rhabdomyosarcoma cell line JR1.

Recommended Dilutions

Western Blot 1:1000, Immunohistochemistry-Paraffin 1:20, Immunocytochemistry/Immunofluorescence 1:20, Immunohistochemistry

References

Fukuda A, Morris JP 4th, Hebrok M Bmi1 is required for regeneration of the exocrine pancreas in mice Gastroenterology 2012 Sep [PMID: 22609312] (IHC, ICC/IF, Mouse

Images

Western Blot: Vimentin Antibody (J144) [NB100-74564] - Fig 1: shows a Western blot of vimentin in rat brain cells.



Limitations: This product is for research use only and is not approved for use in humans or in clinical diagnosis. Products are guaranteed for six months from the date of receipt except for peptides and proteins which are guaranteed for 3 months. **For more information on our guarantee, please visit www.novusbio.com/guarantee.**

Novus USA
 8100 Southpark Way, A-8
 Littleton, CO 80120
 p) 888-506-6887
 p) 303-730-1950
 f) 303-730-1966
novus@novusbio.com
Novus Canada
 461 North Service Road West,
 Unit B37
 Oakville, ON L6M 2V5
 p) 855-668-8722
 f) 905-827-6402
canada@novusbio.com
Novus Europe
 12 Cambridge Science Park
 Cambridge, UK CB4 0FQ
 UK: p) +44-1223-426-001, f) +44-871-971-1635
 DE: p) +49-6922-22340-60, f) +49-0800-58926-79
 IT: p) +39-02-4032-6786, f) +39-02-4032-6340
 FR: p) +33-1-76-77-45-30, f) +33-1-76-77-45-31
europe@novusbio.com
