

NB100-62362**Astrovirus Antibody (SV10 (BGN/07/8610))****Unit Size**

0.1 mg

Concentration

1.0 mg/ml

Storage

Store at 4C short term. Aliquot and store at -20C long term. Avoid freeze-thaw cycles.

Applications

ELISA

Species

Virus

Host

Mouse

Clonality

Monoclonal

Isotype

IgG3

Purity

Protein G purified

Preservative

0.09% Sodium Azide

Specificity/Sensitivity

NB100-62362 is specific for astrovirus serotype 1, reactivity with other serotypes has not been determined.

Immunogen

Purified human astrovirus serotype 1, cultured in HT29 or CACO2 cells.

Recommended Dilutions

ELISA

Buffer

Phosphate buffered saline

Uses

This antibody is useful for ELISA

ImagesThis product does not currently have an image. Earn rewards by submitting your image of this product. Submit a review with your image here: www.novusbio.com/NB100-62362

Updated 3/9/2013 2.0

Limitations: This product is for research use only and is not approved for use in humans or in clinical diagnosis. Products are guaranteed for six months from the date of receipt except for peptides and proteins which are guaranteed for 3 months. For more information on our guarantee, please visit www.novusbio.com/guarantee.

Novus USA

8100 Southpark Way, A-8
 Littleton, CO 80120
 p) 888-506-6887
 p) 303-730-1950
 f) 303-730-1966
novus@novusbio.com

Novus Canada

461 North Service Road West,
 Unit B37
 Oakville, ON L6M 2V5
 p) 855-668-8722
 f) 905-827-6402
canada@novusbio.com

Novus Europe

12 Cambridge Science Park
 Cambridge, UK CB4 0FQ
 UK: p) +44-1223-426-001, f) +44-871-971-1635
 DE: p) +49-6922-22340-60, f) +49-0800-58926-79
 IT: p) +39-02-4032-6786, f) +39-02-4032-6340
 FR: p) +33-1-76-77-45-30, f) +33-1-76-77-45-31
europe@novusbio.com

