

NB100-1772**Avidin Antibody [HRP]****Unit Size**

2 mg

Concentration

10 mg/ml

Storage

Store at 4C short term. Aliquot and store at -20C long term. Avoid freeze-thaw cycles.

Applications

WB, ELISA, IHC, IHC-P

Species

All Species

Host

Rabbit

Clonality

Polyclonal

Conjugate

HRP

Purity

IgG purified

Preservative

0.01% Gentamicin Sulfate

Specificity/Sensitivity

No cross reactivity occurs against Streptavidin.

Immunogen

Avidin [Hen Egg White]

Recommended Dilutions

ELISA 1:10000 - 1:50000, Immunohistochemistry 1:500 - 1:2000, Western Blot 1:2000 - 1:5000, Immunohistochemistry-Paraffin

Buffer

0.02M potassium phosphate, 0.15M NaCl [pH 7.2] and 10 mg/ml BSA

Uses

This product has been assayed against 1.0 ug of Avidin [Hen Egg White] in a standard capture ELISA using ABTS ELISA PEROXIDASE SUBSTRATE for 30 minutes at room temperature. A working dilution of 1:7,000 - 1:27,000 of the reconstitution concentration is suggested for this product.

ImagesThis product does not currently have an image. Earn rewards by submitting your image of this product. Submit a review with your image here: www.novusbio.com/NB100-1772

Updated 3/9/2013 2.0

Limitations: This product is for research use only and is not approved for use in humans or in clinical diagnosis. Products are guaranteed for six months from the date of receipt except for peptides and proteins which are guaranteed for 3 months. **For more information on our guarantee, please visit www.novusbio.com/guarantee.**

Novus USA

8100 Southpark Way, A-8
 Littleton, CO 80120
 p) 888-506-6887
 p) 303-730-1950
 f) 303-730-1966
novus@novusbio.com

Novus Canada

461 North Service Road West,
 Unit B37
 Oakville, ON L6M 2V5
 p) 855-668-8722
 f) 905-827-6402
canada@novusbio.com

Novus Europe

12 Cambridge Science Park
 Cambridge, UK CB4 0FQ
 UK: p) +44-1223-426-001, f) +44-871-971-1635
 DE: p) +49-6922-22340-60, f) +49-0800-58926-79
 IT: p) +39-02-4032-6786, f) +39-02-4032-6340
 FR: p) +33-1-76-77-45-30, f) +33-1-76-77-45-31
europe@novusbio.com

