

NB100-2379R**OCT4 Antibody [DyLight 550]****Unit Size**

0.1 ml

Concentration

0.85 mg/ml

Storage

Store at 4C in the dark.

Applications

WB

Species

Human, Mouse, Bovine, Primate, Porcine

Host

Rabbit

Clonality

Polyclonal

Conjugate

DyLight 550

Purity

Affinity purified

Preservative

No Preservative

Marker

Embryonic Stem Cell Marker

Specificity/Sensitivity

OCT4 - Embryonic Stem Cell Marker

Immunogen

A synthetic peptide made to an internal portion of the human OCT4 protein sequence (between residues 100-200).

Recommended Dilutions

Western Blot 2 ug/ml

Buffer

50mM sodium borate

Uses

By Western blot a band is seen at ~40 kDa.

ImagesThis product does not currently have an image. Earn rewards by submitting your image of this product. Submit a review with your image here: www.novusbio.com/NB100-2379R

Updated 3/9/2013 2.0

Limitations: This product is for research use only and is not approved for use in humans or in clinical diagnosis. Products are guaranteed for six months from the date of receipt except for peptides and proteins which are guaranteed for 3 months. **For more information on our guarantee, please visit www.novusbio.com/guarantee.**

Novus USA

8100 Southpark Way, A-8
 Littleton, CO 80120
 p) 888-506-6887
 p) 303-730-1950
 f) 303-730-1966
novus@novusbio.com

Novus Canada

461 North Service Road West,
 Unit B37
 Oakville, ON L6M 2V5
 p) 855-668-8722
 f) 905-827-6402
canada@novusbio.com

Novus Europe

12 Cambridge Science Park
 Cambridge, UK CB4 0FQ
 UK: p) +44-1223-426-001, f) +44-871-971-1635
 DE: p) +49-6922-22340-60, f) +49-0800-58926-79
 IT: p) +39-02-4032-6786, f) +39-02-4032-6340
 FR: p) +33-1-76-77-45-30, f) +33-1-76-77-45-31
europe@novusbio.com

