

35440002

Sumo 2 Antibody

Unit Size

0.05 mg

Concentration

Please see the vial label for concentration.

Storage

Store at -20C. Avoid freeze-thaw cycles.

Applications

WB, ELISA

Species

Human

Host

Rabbit

Clonality

Polyclonal

Purity

Affinity purified

Preservative

No Preservative

Specificity/Sensitivity

This product is specific for Human SUMO2.

Immunogen

This antibody is specific for the N Terminus Region of the target protein.

Recommended Dilutions

ELISA, Western Blot 1:5000-1:20000

Buffer


20 mM Potassium Phosphate, 150 mM Sodium Chloride, pH 7.0

Uses

This antibody is useful in ELISA and Western Blot.

Images

ELISA: Sumo 2 Antibody [35440002]



Notes

Manufactured by SDIX's proprietary Genomic Antibody Technology™. GAT [FAQs](#).

Updated 3/9/2013 2.0

Limitations: This product is for research use only and is not approved for use in humans or in clinical diagnosis. Products are guaranteed for six months from the date of receipt except for peptides and proteins which are guaranteed for 3 months. **For more information on our guarantee, please visit www.novusbio.com/guarantee.**

Novus USA

8100 Southpark Way, A-8
 Littleton, CO 80120
 p) 888-506-6887
 p) 303-730-1950
 f) 303-730-1966
novus@novusbio.com

Novus Canada

461 North Service Road West,
 Unit B37
 Oakville, ON L6M 2V5
 p) 855-668-8722
 f) 905-827-6402
canada@novusbio.com

Novus Europe

12 Cambridge Science Park
 Cambridge, UK CB4 0FQ
 UK: p) +44-1223-426-001, f) +44-871-971-1635
 DE: p) +49-6922-22340-60, f) +49-0800-58926-79
 IT: p) +39-02-4032-6786, f) +39-02-4032-6340
 FR: p) +33-1-76-77-45-30, f) +33-1-76-77-45-31
europe@novusbio.com

