

NB100-186G**Tankyrase Antibody [DyLight 488]****Unit Size**

0.1 ml

Concentration

1.0 mg/ml

Storage

Store at 4C in the dark.

Applications

WB

Species

Human

Host

Rabbit

Clonality

Polyclonal

Conjugate

DyLight 488

Purity

Affinity purified

Preservative

No Preservative

Specificity/Sensitivity

This is specific for Tankyrase.

Immunogen

A synthetic peptide made to a region of human Tankyrase within residues 250-350. The actual peptide sequence is proprietary.

Recommended Dilutions

Western Blot 1:500 to 1:1000

Buffer

50mM sodium borate

Uses

In western blot this antibody recognizes an endogenous band at ~150 kDa in whole cell extract and a band at ~180 kDa in baculovirus-derived his-tagged protein.

ImagesThis product does not currently have an image. Earn rewards by submitting your image of this product. Submit a review with your image here: www.novusbio.com/NB100-186G

Updated 3/9/2013 2.0

Limitations: This product is for research use only and is not approved for use in humans or in clinical diagnosis. Products are guaranteed for six months from the date of receipt except for peptides and proteins which are guaranteed for 3 months. **For more information on our guarantee, please visit www.novusbio.com/guarantee.**

Novus USA

8100 Southpark Way, A-8
 Littleton, CO 80120
 p) 888-506-6887
 p) 303-730-1950
 f) 303-730-1966
novus@novusbio.com

Novus Canada

461 North Service Road West,
 Unit B37
 Oakville, ON L6M 2V5
 p) 855-668-8722
 f) 905-827-6402
canada@novusbio.com

Novus Europe

12 Cambridge Science Park
 Cambridge, UK CB4 0FQ
 UK: p) +44-1223-426-001, f) +44-871-971-1635
 DE: p) +49-6922-22340-60, f) +49-0800-58926-79
 IT: p) +39-02-4032-6786, f) +39-02-4032-6340
 FR: p) +33-1-76-77-45-30, f) +33-1-76-77-45-31
europe@novusbio.com

